


10	9	8	7	6	5	4	3	2	1
F	MAT'L NO.	ENG NO.	STUD SIZE	$\phi''S''$ $\pm.010 (0.25)$					F
191640069	SC-241-06	6	.146 (3.71)						
191640070	SC-241-08	8	.173 (4.39)						
191640071	SC-241-10	10	.198 (5.03)						



NOTE(S):

- 1 TERMINAL MATERIAL: COPPER ALLOY
- 2 FINISH: ELECTRO TIN PLATE
- 3 INSULATION MATERIAL: HEAT SHRINKABLE TUBING

WITH HOTMELT ADHESIVE INNER LINER.

COLOR: YELLOW

4 MWID = MAXIMUM WIRE INSULATION DIAMETER.

5. PARTS ARE RoHS COMPLIANT.

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						molex	
		DIMENSION UNITS		SCALE		CURRENT REV DESC: DIM WAS MAX			
		INCH/MM		NTS					
				GENERAL TOLERANCES (UNLESS SPECIFIED)					
∇	0			MM INCH					
∇	0			4 PLACES \pm					
∇	0			3 PLACES \pm					
∇	0			2 PLACES \pm					
∇	0			1 PLACE \pm					
∇	0			0 PLACES \pm					
				ANGULAR TOL \pm °					
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					
				THIRD ANGLE PROJECTION		DRAWING		SERIES	
				B-SIZE		19164			
				MATERIAL NUMBER		CUSTOMER			
				GENERAL MARKET					
				1 OF 1					