



NC7MD-L-B-1




Universal D-size metal body XLR panel mount series. UL recognized component.

7 pole male receptacle, solder cups, black metal housing, gold contacts

Features & Benefits

- Robust "D" metal shell
- Standardized D sized 24 mm panel cutout
- Solder cups on 3 - 7 pole version



Product

Connector Type

Gender

XLR

male

Electrical

Capacitance between contacts	$\leq 9 \text{ pF}$
Contact resistance	$\leq 5 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 2 \text{ G}\Omega$ (initial)
Insulation resistance	$> 1 \text{ G}\Omega$ (after damp heat test)
Rated current per contact	5 A
Rated voltage	50 V

Mechanical

Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	> 1000 mating cycles
Wire size	max. 1.0 mm^2
Wire size	max. 18 AWG
Wiring	Solder contacts
Locking device	latch lock
Mounting direction	front & rear
Chassis shape	D

Material

Contact plating	$0.2 \text{ }\mu\text{m}$ Au hard alloy over $2 \text{ }\mu\text{m}$ Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Steel Ck67
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Black chromium

Environmental

Approvals	UL
Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	$-30 \text{ }^{\circ}\text{C}$ to $+80 \text{ }^{\circ}\text{C}$