



1179




1179-0-00-XX-00-00-33-0
Solder mount in .044 mounting hole

9872




9872-0-00-XX-00-00-33-0
Solder mount in .049 mounting hole

2381




2381-0-00-XX-00-00-33-0
Solder mount in .054 mounting hole

9265




9265-0-00-XX-00-00-38-0
Solder mount in .063 mounting hole

6142




6142-0-00-XX-00-00-33-0
Solder mount in .064 mounting hole

9022



9022-0-00-XX-00-00-33-0
Solder mount in .066 mounting hole

8086



8086-0-00-XX-00-00-33-0
Solder mount in .079 mounting hole

SPECIFICATIONS

PIN MATERIAL:
Brass Alloy 360, 1/2 Hard
(Except where noted)

DIMENSION IN INCHES
TOLERANCES ON:
 LENGTHS: $\pm .005$
 DIAMETERS: $\pm .002$
 ANGLES: $\pm 2^\circ$

ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 3X - 0

BASIC PART #



SPECIFY PIN FINISH:

01 200μ" TIN/LEAD OVER NICKEL
80 200μ" TIN OVER NICKEL 
15 10μ" GOLD OVER NICKEL 
21 20μ" GOLD OVER NICKEL 
34 50μ" GOLD OVER NICKEL 