


PHONO PLUGS

- Mates with .125 (3.2) diameter jacks

STRAIN RELIEF LUG CRIMPS TO WIRE INSULATION




CAT. NO. 565

MATERIAL:

Shell: Steel, Tin Plate
Pin: Brass, Nickel Plate

CONVENTIONAL TYPE




CAT. NO. 561

MATERIAL:

Shell: Brass, Nickel Plate
Pin: Brass, Nickel Plate

CRIMP OR SOLDER TYPE EXTRA LONG HANDLE



CAT. NO. 567

MATERIAL:

Shell: Steel, Tin Plate
Pin: Brass, Nickel Plate


BINDING POSTS

All Keystone binding posts are designed to prevent accidental contact with current carrying parts. They feature a "limited opening" captivated head to insure safety. Ideal for audio circuitry, R.F. circuitry, oscilloscopes, power supplies and various other applications.


These multi-purpose binding posts feature high current rating, captivated heads and anti-rotation stud mounting.

Note: Binding Posts accept .175" (4.5) Banana Plugs, .080" (2.08) Tip Plugs, Spade Lugs, Alligator Clips, Wires and EZ hooks.

STANDARD BINDING POST



Mounting Detail



MATERIAL:

Stud: Brass per QQ-B-626

Plating: Silver Plate

Insulation: Nylon


Current Rating: 15 Amps

Stud to Panel Capacitance: 3.3 pF Nominal

For panels up to .281 (7.1) thick

CAT. NO.	COLOR
7004	RED
7005	BLACK

UNINSULATED BINDING POST



MATERIAL:

Stud: Brass per QQ-B-626

Plating: Nickel Plate


Insulation: Nylon

Current Rating: 15 Amps, 1000V AC Working


For panels up to .313 (8.0) thick

CAT. NO.	COLOR
7006	RED
7007	BLACK

STANDARD DUAL HEX HEAD



Mounting Detail



MATERIAL:


Stud: Brass per ASTM B-16.

Insulation: Nylon


Current Rating: 30 Amps, 1000V AC Working

GOLD PLATE		NICKEL PLATE	
CAT. NO.	THREAD	CAT. NO.	THREAD
4108	8-32	7018	8-32
4109	10-32	7019	10-32

STANDARD HEX HEAD



Mounting Detail



MATERIAL:

Stud: Brass per ASTM B-16.

Insulation: Nylon

Current Rating: 30 Amps, 1000V AC Working

GOLD PLATE			NICKEL PLATE		
CAT. NO.	THREAD	COLOR	CAT. NO.	THREAD	COLOR
4096	8-32	RED	4091	8-32	RED
4097	8-32	BLACK	4092	8-32	BLACK
7016	10-32	RED	4093	10-32	RED
7017	10-32	BLACK	4094	10-32	BLACK
7023	10-32	WHITE	4198	10-32	WHITE
7024	10-32	YELLOW	4199	10-32	YELLOW