

Micrometers Mechanical

LINEAR *TOOLS* micrometers are precision instrument for measuring small distances.

Special care in design and workmanship create a long lasting precision tool.

General specification for all mechanical micrometers unless otherwise stated:

- Accuracy conforms to DIN 863
- Hammertone blue baked enamel finish
- Tungsten carbide measuring faces
- Non-glare satin chrome barrel & sleeve
- Microfine graduations for accurate reading
- Micrometers above 25mm & 1" supplied with setting rod
- Spindle locking lever
- Spindle diameter 6.5mm
- Standard models have ratchet thimble
- Supplied in fitted case with adjustment tools
- Spindle diameter: 6.5mm
- Flatness of measuring faces: 0.00076mm
- Parallelism of measuring faces: 0.000125mm

Micrometer graduations:

- Metric: 0.01mm
- Imperial: 0.001"

100 Series Standard



110 Series Digit



Spline



Disc



Screw Thread



Depth



All measuring tools (where applicable standard exists) can be supplied with UKAS certificate, prices upon request.

Outside Micrometers Metric DIN 863

TECHNICAL:

- Accuracy conforms to DIN 863
- Hammertone blue baked enamel finish
- Tungsten carbide measuring faces
- Non-glare satin chrome barrel & sleeve
- Microfine graduations for accurate reading
- Models above 25mm/1" supplied with setting rod
- Spindle locking lever
- Spindle diameter 6.5mm
- Standard models have ratchet thimble
- Supplied in fitted case with adjustment tools
- Flatness of measuring faces: 0.00076mm
- Parallelism of measuring faces: 0.000125mm

Micrometer graduations:

- Metric: 0.01mm
- Imperial: 0.001"



Order Code	Description/ Size	Order Code	Description/ Size
50-100-025	0-25mm	50-100-001	0-1"
50-100-050	25-50mm	50-100-002	1-2"
50-100-075	50-75mm	50-100-003	2-3"
50-100-100	75-100mm	50-100-004	3-4"
50-100-125	100-125mm	50-100-005	4-5"
50-100-150	125-150mm	50-100-006	5-6"
50-100-175	150-175mm	50-100-007	6-7"
50-100-200	175-200mm	50-100-008	7-8"
50-100-225	200-225mm	50-100-009	8-9"
50-100-250	225-250mm	50-100-010	9-10"
50-100-275	250-275mm	50-100-011	10-11"
50-100-300	275-300mm	50-100-012	11-12"

