

Plug-In

Bandpass Filter

50Ω Constant Impedance 41 to 58 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Pin Connections


INPUT	1
OUTPUT	6
GROUND	2,3,4,5,7,8
CASE GROUND	2,5,7,8

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F
.770	.800	.385	.400	.370	.400
19.56	20.32	9.78	10.16	9.40	10.16
G	H	J	K	wt	
.200	.20	.14	.031	grams	
5.08	5.08	3.56	0.79	5.2	



Features

- low VSWR in pass & stopbands, 1.3:1 typ.
- shielded welded case, hermetically sealed
- custom designs available

Applications

- harmonic rejection
- lab use
- military/hi-rel applications

PIF-50+
PIF-50



CASE STYLE: A01
PRICE: \$17.20 ea. QTY: 1-9


+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.


Bandpass Filter Electrical Specifications

MODEL NO.	CENTER FREQ. (MHz)	PASSBAND (MHz)	STOPBANDS		VSWR, 1.3:1 Typ. TOTAL BAND (MHz)
		(loss<1 dB)	(loss > 10 dB) at MHz	(loss > 20 dB) at MHz	
PIF-50(+)	50	41-58	11.5 & 200	3.1 & 350	DC-440

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
$\bar{x}$	σ			
1.0	33.62	0.2	3.1	1.540
1.4	30.60	0.2	3.2	2.572
1.8	28.39	0.2	5.9	3.434
2.3	26.60	0.2	8.7	3.800
2.7	25.16	0.2	11.4	3.893
3.1	23.91	0.2	11.6	3.910
4.0	21.72	0.3	18.2	4.448
9.0	14.63	0.2	24.4	5.257
11.5	12.44	0.2	31.1	6.290
20.0	7.25	0.2	32.2	6.428
23.7	5.61	0.2	41.0	7.293
27.3	4.18	0.2	41.7	7.342
31.0	2.95	0.2	43.9	7.325
41.0	0.70	0.1	46.2	7.197
45.5	0.28	0.1	48.7	6.905
50.0	0.21	0.1	51.3	6.571
53.0	0.34	0.1	53.1	6.309
77.0	3.12	0.1	55.9	5.874
80.0	3.52	0.1	57.9	5.441
120.0	7.84	0.1	58.9	5.242
160.0	10.99	0.2	77.6	2.769
200.0	13.61	0.2	117.5	1.114
250.0	16.51	0.2	119.5	1.093
316.7	20.38	0.4	160.3	0.679
350.0	22.46	0.4	200.7	0.525
390.0	25.29	0.6	246.9	0.414
402.5	26.25	0.7	251.2	0.408
415.0	27.29	0.8	298.5	0.306



Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

REV. A
M98898
SIF-50
060710