







THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

DESCRIPTION	MATERIAL	FINISH
CENTER CONTACTS	BRASS	GOLD
OUTER CONTACT	BRASS	NICKEL
BODY	BRASS	NICKEL
CRIMP FERRULE	COPPER	NICKEL
GASKET	RUBBER	---
INSULATOR	TEFLON	---
RETAINING RING	Phosphor Bronze	---

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	Initial Release	07/08/06	K.Burgner
B	Updated format and Connector info ECN#4368	11/11/09	B.Puchaski
C	Removed Insulator Pad, Update Body ECN#4692	04/16/10	B.Puchaski



**RECOMMENDED
FERRULE
CRIMP SIZE**

**RECOMMENDED
PIN
CRIMP SIZE**

**RECOMMENDED CABLE
STRIPPING**

NOTES:

ELECTRICAL:


IMPEDENCE: 50 OHMS
WITHSTAND VOLTAGE: 2500V
FREQUENCY RANGE: 0~6 GHz
VSWR: ≤1.50 @ 0~6 GHz
DURABILITY: ≥ 500 CYCLE
CABLE RETENTION: > 40 POUNDS

MISCELLANEOUS:

COMPONENTS SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATIONS PS-0031.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

RoHS Compliant

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005 ANGULAR TOLERANCES: ALL = ± 1° PROJECTION 	APPROVALS		DATE		 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY B.Puchaski		11/11/09		
	CHECKED BY M.Audas		11/11/09		CATEGORY CONNECTOR
	APPROVED BY M.Audas		11/11/09		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION N STRAIGHT MALE CRIMP FOR RG8 / LMR400		
COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. ANM-1406	REV. C
		SCALE: NONE CAD FILE: ANM-1406.SLDDRW			SHEET 1 OF 1