







RECOMMENDED P.C.B. LAYOUT



CIRCUIT: SPST



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. RATING: 50mA, @12V DC
5. TRAVEL: 0.25 ± 0.1 mm
6. OPERATING FORCE: 160 ± 50 gf
7. CONTACT RESISTANCE: 100 milliohms Max.
8. ELECTRICAL LIFE: 100,000 CYCLES MIN.
9. ▲ DESIGNATE MAJOR FEATURE
- ▲ 10. ACTUATOR COLOR: BROWN
- ▲ 11. HOUSING COLOR: BLACK

C	18677	LEG TOLERANCE WAS +/- 0.1	10/9/09	BLR
B	16112	ADD GOLD DOME NOTE	6/6/06	CT
A	12918	RELEASED	3/17/03	AR
REV.	ECN No.	DESCRIPTION	DATE	CHKD

		 E-SWITCH®		 LAMB™ INDUSTRIES			
TITLE							
TL 1105W F160 R							
SCALE		DATE		DR		DWG	
4:1		10/9/09		BLR		P020225	
						REV	
						C	