

6

5

4

3



2

1



Rev	AWO #	Description	Date	Appr
-		RELEASED	4/12/05	

APPROVED: _____

DATE: _____ TITLE: _____



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 5 Amps max

Contact resistance: 10 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20
A = .156 [3.96] x No. of Positions + .012 [0.30]
B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
HOLES		Ø.X		TITLE .156 [3.96] POWER HEADER STRAIGHT, WITH LOCK POLARIZER			
.X ± .10		Ø.XX ± .10					
.XX ± .020		Ø.XXX ± .015					
.XXX ± .015		Ø.XXX ± .010					
APPROVALS		DATE					
DRAWN	SS	4/12/05					
CHECKED				SIZE	PART NO.	REV.	
APPROVED				X	LHB-XX-SA1	-	
REF:				SCALE:	NTS	SHEET	1 OF 1