



DO NOT SCALE
FROM THIS PRINT

- NOTES:
1. MIN. PUSHOUT FORCE: .5 lb.
 2. COPLANARITY: .004=POS 05 THRU 26
.006=POS 27 THRU 50
 3. (C) REPRESENTS CRITICAL DIMENSION
 4. TUBE ALL POSITIONS.
 5. PINS CAN BE ORIENTED IN ANY DIRECTION;
BOTH ROWS MUST FACE SAME WAY.
 6. SEE NOTCH FOR PROPER ORIENTATION.

FIG. 1

-T1: THROUGH HOLE/STRAIGHT MODIFIED

SFM-XX-D-XX



SFC-1XX-XX-XX-D-XX

NO. OF POSITIONS
ALL POSITIONS AVAILABLE
-5 THRU -50
USE BODY: (SFM-XX-D-XX)

LEAD STYLE

- T1: THROUGH HOLE (PHOS BRONZE)
USE CONTACT: (C-119-01-XX)
(SEE FIG. 1, SHT. 1)
-T2: SURFACE MOUNT (PHOS BRONZE)
USE CONTACT: (C-119-02-XX)
(SEE FIG. 2, SHT. 1)

PLATING SPECIFICATION

- F: FLASH SELECTIVE GOLD
-L: LIGHT SELECTIVE GOLD
-FM: FLASH SELECTIVE GOLD/MATTE TIN TAILS
-LM: LIGHT SELECTIVE GOLD/MATTE TIN TAILS

OPTIONS

- (LEAVE BLANK FOR STANDARD
AND USE SFM-XX-D)
-A: ALIGNMENT PIN (USE SFM-XX-D-A)
(SEE FIGURE 5, SHT. 2)
-LC: LOCKING CLIP (SEE FIGURE 6)
(USE (2) LC-05-TM & SFM-XX-D-LC)
(AVAILABLE ON ALL LEADS)
-TR: TAPE & REEL
(SEE FIG 4, SHT. 2)
-K: POLYAMIDE FILM PAD (.005 [.13]
THICKNESS WITH SILICONE ADHESIVE)
(SEE FIG 3) (USE K-500-300)


BODY SPECIFICATION

- D: DOUBLE ROW

TABLE 1

SUFFIX	TAIL LENGTH "A"	TAIL WIDTH "B"
-T1	.120 [3.05]	.020 [.51]

DETAIL 'A'
(ALTERNATE CONSTRUCTION)
SCALED 3x



DIFFERENT AS SHOWN OTHERWISE SAME AS FIG. 1






FIG. 2

-T2: SURFACE MOUNT



NOTE: "R" = USED MEASURED DIMENSION (REF)
"S" = {("R" - .1575 [4.00])/2} ± .020 [.51]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:
BRATCHER 5-25-01

SFC-1XX-XX-XX-D-XX
SHEET 1 OF 2

MISC\MRKT
SFC-MKT