




Fig. 1




Fig. 2




Fig. 3




Fig. 4




Fig. 5

- Receptacles accept .030" diameter and .025" square pins.
- Pin headers use MM# 5016 pins. (See page 173 for details)
- Low profile sockets use MM# 1303 pins. (See page 148 for details)



Ordering Information

Fig. 1	Single Row	Low Profile Pin Header						
	800-XX-0 _ _ -10-002000							
	Specify # of pins	└───> 01-64						
Fig. 2	Double Row	Low Profile Pin Header						
	802-XX-0 _ _ -10-002000							
	Specify # of pins	└───> 02-64						
		XX= Plating Code See Below		For RoHS compliance, select  plating code. For the gold option (XX=10) also change part number from 80X-XX-0XX-10-002000 to 80X-10-0XX-10-002100				
SPECIFY PLATING CODE XX=		10 	90	40 				
Pin Plating 		10μ" Au	200μ" Sn/Pb	200μ" Sn				
Fig. 3	Single Row	Low Profile Socket (short insulator)						
	801-XX-0 _ _ -10-002000							
	Specify # of pins	└───> 01-64						
Fig. 4	Single Row	Low Profile Socket (long insulator)						
	801-XX-0 _ _ -10-012000							
	Specify # of pins	└───> 01-36						
Fig. 5	Double Row	Low Profile Socket						
	803-XX-0 _ _ -10-002000							
	Specify # of pins	└───> 02-72						
		XX= Plating Code See Below		For RoHS compliance, select  plating code. For the all gold option (XX=13) also change part number from 80X-XX-0XX-10-0X2000 to 80X-13-0XX-10-0X2100				
SPECIFY PLATING CODE XX=		13 		93	99		43 	44 
Sleeve (Pin) 		10μ" Au		200μ" Sn/Pb	200μ" Sn/Pb		200μ" Sn	200μ" Sn
Contact (Clip) 		30μ" Au		30μ" Au	200μ" Sn/Pb		30μ" Au	200μ" Sn