

➤ OVERVIEW:

ASGTX temperature compensated Crystal Oscillators are designed to accommodate a broad breadth of Precision TCXO requirements, without NRE and extended lead-times. This oscillator series is designed and manufactured by Abracon Corporation and is available to order from 1pc to high volume production quantities.

- **1-5 day quick-turn availability of a TCXO/VCTCXO with LVCMOS output, Any frequency between 10MHz & 250MHz**

For example, if a reference oscillator requirement calls out 49.7521MHz; ± 1.00 ppm TCXO/VCTCXO with **LVCMOS** output, ASGTX can be configured and shipped within 1-5 days and in most cases, same day if order is received before noon. Customers with low-to-mid annual volume requirements find it difficult to procure custom frequency TCXO/VCTCXO's without costly NRE charges and/or long lead-times (≥ 12 weeks).

- **1-5 day quick turn availability of a TCXO/VCTCXO requiring LVDS or LVPECL Differential output, Any frequency between 10MHz to 1.50GHz**

ASGTX is available with either **LVDS or LVPECL** output, from **10MHz to 1.50GHz**; at any desired frequency, such as 149.875MHz, 1.00GHz, 1.5GHz, etc. with as tight as ± 1.00 ppm stability over temperature. No other solution in the marketplace currently offers such capability, especially in a small form-factor of 9.0x7.0x2.24 mm.

ASGTX is suitable for a wide variety of precision timing applications where TCXO/VCTCXO's are typically employed. In addition, for high frequency LO requirements, traditionally customers have relied on SAW based oscillators. Such devices are only available at a few fixed frequencies, such as 915MHz, 1.0GHz, etc. They are typically in 9x14mm or bigger packages and vary as much as ± 100 ppm over temperature.

Although ASGTX series will be slightly less favorable in phase noise performance compared to SAW based oscillators, it offers the following key advantages:

- o ± 1.00 ppm stability over -30°C to $+70^{\circ}\text{C}$ & ± 2.00 ppm stability over -40°C to $+85^{\circ}\text{C}$
- o **Any carrier frequency** between 10MHz & 1.50GHz
- o LVCMOS Output (10MHz to 250MHz) **or** LVDS / LVPECL Output (10MHz to 1.50GHz)
- o Small form-factor of 9.0x7.0x2.24 mm
- o No NRE or lead-time

➤ FEATURES:

- 10MHz to 1.50GHz, any Carrier Frequency in differential mode (LVDS or LVPECL)
- 10MHz to 250MHz, any Carrier Frequency in LVCMOS mode
- -40°C to $+85^{\circ}\text{C}$ operating temperature range
- ± 1.0 ppm stability over -30°C to $+70^{\circ}\text{C}$ and ± 2.0 ppm stability over -40°C to $+85^{\circ}\text{C}$
- Minimum guaranteed pull ability of ± 10 ppm in VCTCXO mode
- Good Phase Noise, excellent Harmonics and Spurious content
- Guaranteed rms jitter of 1.80ps maximum @ 1.50GHz carrier (LVDS mode)
- Immediate availability, 5-day maximum lead-time for small quantities

➤ APPLICATIONS:

- 40G & 100G Ethernet
- WiMax,
- LTE, BTS
- CATV, LAN, LMDS
- Point-to-Point communication networks




Configurable High Performance SMD TCXO/VCTCXO

ASGTX



RoHS/RoHS II Compliant



9.0 x 7.0 x 2.24 mm

KEY ELECTRICAL SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency:	LVC MOS	10		250	MHz	
	LVDS	10		1500		
	LVPECL	10		1500		
Operating Temperature:		-40		+85	°C	
Storage Temperature:		-40		+85	°C	
Frequency Stability:						
Initial Set Tolerance		-1.50	$\leq \pm 1.00$	+1.50	ppm	1 hour after reflow
Stability over operating temperature*	-30°C to +70°C	-1.00		+1.00	ppm	Option "1"
	-40°C to +85°C **	-2.00		+2.00		Option "2"
Aging @ 25°C after one year		-1.00		+1.00	ppm	
Supply Voltage (V _{dd}):		3.135	3.300	3.465	V	
Startup Time:				3	ms	
Control Voltage***:		0		V _{dd}	V	In VCTCXO Mode
Frequency Pull:		± 10			ppm	
Phase jitter RMS [$t_{jit}(\)$] **** (12kHz to 20MHz)			<1.00	1.80	ps	Frequency dependent


Notes

- * *Relative to measured frequency post reflow*
- ** *Please contact Abracon for ± 1.00 ppm frequency stability over -40°C to +85°C*
- *** *Center Control Voltage value is either 1.28V ± 0.20 V or, 1.55V ± 0.20 V for the device to be with-in ± 1.50 ppm of final frequency, 1-hour post reflow*
- **** *1.8ps max is guaranteed for LVC MOS and LVDS output modes. For LVPECL mode at carrier frequency greater than 1.289GHz, the maximum RMS jitter is 3.0ps*

Key Electrical Specifications – LVC MOS

Parameters		Minimum	Typical	Maximum	Units	Notes
Supply Current (I _{dd}):				45	mA	Frequency dependent
Output Load:				15	pF	
Output Logic Level:	V _{OH}	0.9*V _{dd}			V	
	V _{OL}			0.1*V _{dd}	V	
Rise Time (Tr):				1000	ps	
Fall Time (Tf):				1000	ps	
Duty Cycle:		45		55	%	@1/2V _{dd}





9.0 x 7.0 x 2.24 mm

Key Electrical Specifications – LVPECL

Parameters		Minimum	Typical	Maximum	Units	Notes
Supply Current (I_{dd})				60	mA	With typical LVPECL output termination
Output Logic Level	V_{OH}	$V_{dd}-1.03$		$V_{dd}-0.60$	V	
	V_{OL}	$V_{dd}-1.85$		$V_{dd}-1.60$	V	
Rise Time (T_r):				350	ps	
Fall Time (T_f):				350	ps	
Differential Duty Cycle:		45		55	%	$DODC_{LVPECL}$

Key Electrical Specifications – LVDS

Parameters		Minimum	Typical	Maximum	Units	Notes
Supply Current (I_{dd})				40	mA	With typical LVDS output termination
Differential Output Voltage (V_{OD})		175	350		mV	
V_{OD} Magnitude Change (ΔV_{OD})				50	mV	
Offset Voltage (V_{OS})			1.25		V	
V_{OS} Magnitude Change (ΔV_{OS})				50	mV	
Rise Time (T_r):				350	ps	
Fall Time (T_f):				450	ps	
Differential Duty Cycle:		45		55	%	ODC_{LVDS}

➤ OPTIONS & PART IDENTIFICATION:

ASGTX- - MHz - -

Output Type	
C	LVC MOS
P	LVPECL
D	LVDS

Frequency in MHz	
Please specify the	Frequency in MHz
e.g.	100.000 MHz

Freq. Stability	
1	± 1 ppm over -30 to $+70^\circ\text{C}$
2	± 2 ppm over -40 to $+85^\circ\text{C}$

Packaging	
Blank	Bulk (Qty < 250pcs)
T	1000pcs/Reel
T2	250pcs/Reel


C = LVC MOS	Any Carrier Frequency between 10MHz minimum to 250MHz maximum
P = LVPECL	Any Carrier Frequency between 10MHz minimum to 1.50GHz maximum
D = LVDS	Any Carrier Frequency between 10MHz minimum to 1.50GHz maximum

Configurable High Performance SMD TCXO/VCTCXO

ASGTX




RoHS/RoHS II Compliant




9.0 x 7.0 x 2.24 mm

TYPICAL PHASE NOISE & JITTER CHARACTERISTICS


With LVCMOS Output; 10MHz Carrier




With LVDS Output; 10MHz Carrier



With LVCMOS Output; 25MHz Carrier



With LVDS Output; 25MHz Carrier



Configurable High Performance SMD TCXO/VCTCXO

ASGTX




RoHS/RoHS II Compliant




9.0 x 7.0 x 2.24 mm

TYPICAL PHASE NOISE & JITTER CHARACTERISTICS


With LVC MOS Output; 50MHz Carrier




With LVDS Output; 50MHz Carrier



With LVC MOS Output; 120MHz Carrier



With LVPECL Output; 500MHz Carrier



Configurable High Performance SMD TCXO/VCTCXO

ASGTX




RoHS/RoHS II Compliant




9.0 x 7.0 x 2.24 mm

TYPICAL PHASE NOISE & JITTER CHARACTERISTICS


With LVDS Output; 1.00GHz Carrier



With LVDS Output; 1.2890625GHz Carrier



With LVDS Output; 1.50GHz Carrier



Carrier	RF Output	rms Phase Jitter	Integration Bandwidth
10.00MHz	LVDS	992 fs	12kHz to 5MHz
25.00MHz	LVDS	774 fs	12kHz to 5MHz
50.00MHz	LVDS	768 fs	12kHz to 10MHz
120.00MHz	LVC MOS	1.1 ps	12kHz to 20MHz
500.00MHz	LVPECL	956 fs	12kHz to 20MHz
1.00GHz	LVDS	911 fs	12kHz to 20MHz
1.2890625GHz	LVDS	1.03 ps	12kHz to 20MHz
1.50GHz	LVDS	1.55 ps	12kHz to 20MHz




Configurable High Performance SMD TCXO/VCTCXO

ASGTX




RoHS/RoHS II Compliant




9.0 x 7.0 x 2.24 mm

FREQUENCY STABILITY VS. TEMPERATURE



FREQUENCY PULL VS. CONTROL VOLTAGE (VCTCXO MODE)




Configurable High Performance SMD TCXO/VCTCXO

ASGTX





RoHS/RoHS II Compliant



9.0 x 7.0 x 2.24 mm

OUTLINE DIMENSION:

LVC MOS output




Pin #	Pin Description	
	TCXO	VCTCXO
1	N/C ⁽¹⁾	
2	By-Pass ⁽²⁾	V _c ⁽³⁾
3	GND	
4	RF Output	
5	N/C ⁽¹⁾	
6	V _{dd}	

N/C ⁽¹⁾ = Please leave these pins electrically floating on the end-PCB


By-Pass ⁽²⁾ = In TCXO configuration, it is recommended that a 1,000pF COG by-pass capacitor is connected between Pin#2 and GND

V_c ⁽³⁾ = Please connect external voltage to pull the oscillator frequency

Recommended Land Pattern




Dimensions: inches [mm]



9.0 x 7.0 x 2.24 mm

LVDS/LVPECL output





Pin #	Pin Description	
	TCXO	VCTCXO
1	N/C ⁽¹⁾	
2	By-Pass ⁽²⁾	V _c ⁽³⁾
3	GND	
4	RF Output	
5	Complimentary RF Output	
6	Vdd	

N/C ⁽¹⁾ = Please leave this pin electrically floating on the end-PCB

By-Pass ⁽²⁾ = In TCXO configuration, it is recommended that a 1,000pF COG by-pass capacitor is connected between Pin#2 and GND

V_c ⁽³⁾ = Please connect external voltage to pull the oscillator frequency

Recommended Land Pattern




Dimensions: inches [mm]

9.0 x 7.0 x 2.24 mm




RoHS/RoHS II Compliant

➤ **REFLOW PROFILE:**



➤ **TAPE & REEL:**


Packaging: 1000pcs/reel



Dimensions: mm

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO9001:2008
CERTIFIED



ABRACON CORPORATION

2 Faraday, Suit#B, Irvine, California 92618 **Revised: 10.16.14**

tel:949-546-8000 | fax:949-546-8001

Visit www.abracon.com for Terms & Conditions of Sale