




REVISIONS

ISS	ZONE	DESCRIPTION\PER REQUEST\DATE

CONFIGURATION CONTROL:
NO CHANGES PERMITTED TO DRAWING WITHOUT
PPAP QUALIFIED CUSTOMER APPROVAL

NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER QQ-B-626, ALLOY 360, 1/2 H
; JIS H3250 C 3604BD OR EQUIVALENT
2. GOLD PL. 30 MIN. THICK OVER NICKEL PL. 100 MIN. THICK
OVER COPPER STRIKE
3. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK
OVER COPPER STRIKE
4. TEFLON MIL-P-19468
5. PBT(WITH 15% GLASS FIBER) PER CHANG CHUN GRADE 4115202
OR EQUIVALENT

OR EQUIVALENT						DIMENSIONS ARE IN MILLIMETERS				PART NO.		Amphenol Danbury,CT,USA-Tainan,Taiwan-Shenzehn,China	
6	RING	NOTE 1	NOTE 3	1	FKLR00101A	UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 6-30 = ±0.4 30-120 = ±0.6 120-315 = ±1 315-1000 = ±1.6 1000-2000 = ±2.4				FA1-NXSP-PCB-1			
5	LOCK COVER	NOTE 5		1	SEE TABLE					APPROVED	DATE	TITLE FAKRA EDGECARD PCB MOUNT PLUG	
4	INSULATOR	NOTE 4	NATURAL	1	SMB2071A1-2T-50					CHECKED	DATE		DRAWING NO. KJ-FK1251XX-001-3GT30G-50
3	CONTACT PIN	NOTE 1	NOTE 2	1	SMB125100-003-3						DATE		
2	INSULATOR	NOTE 4	NATURAL	1	SMB125100-003-2T-50					DRAWN	DATE	FILE NO. F:\DWG\FK\FA1\NXSP\PCB\1	
1	BODY	NOTE 1	NOTE 3	1	FK1251CW-001-1	ANGELA							
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	3/1	ISSUE	1				

UNLESS OTHERWISE SPECIFIED TOLERANCES					
0.5-6 = ±0.2					
6-30 = ±0.4					
30-120 = ±0.6					
120-315 = ±1					
315-1000 = ±1.6					
1000-2000 = ±2.4					