



(E)


STRIP MATERIAL NUMBER
84590-0023

FINISH

OVERALL NICKEL 80µ" MINIMUM




SECTION Z-Z



SECTION Y-Y

SELECT PLATING AREA
(CONTACT BEAM ONLY)



NOTES:

1. TERMINAL MATERIAL: COPPER ALLOY .012/0.30 THICK.
HOOD MATERIAL: STAINLESS STEEL .008/0.20 THICK.
2. FINISH: SEE CHART.
3. STRIP TERMINALS ARE REELED AS SHOWN ABOVE,
3000 PARTS PER REEL.
4. TERMINAL FOR USE WITH SERIES XRC CONNECTOR
ASSEMBLIES.
5. ALL DIMENSIONS ARE REFERENCE.
6. ALL MATERIALS AND FINISHES ARE ROHS COMPLIANT.

(E)

WIRE INSULATION O.D. RANGE .075-.150
1.91-3.81

UPDATE NOTES & TABLE EC NO: WNA2008-0139 DRAWN: LUNG 2008/07/26 CHKD: RDOSS 2008/04/21 APPR: RDOSS 2008/04/24	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION 	
				mm	INCH	DRAWN BY RSTONE	DATE 10/19/04	TITLE CONTACT SOCKET (HOODED), 14-18 AWG		
			4 PLACES	± ---	± ---	CHECKED BY APLAZA	DATE 10/19/04			
			3 PLACES	± ---	± .010	APPROVED BY LROTHAUS	DATE 10/19/04			
			2 PLACES	± 0.25	± .02	MOLEX MOLEX INCORPORATED 				
			1 PLACE	± 0.5	± ---					
			ANGULAR ± 1 °		MATERIAL NO.	DOCUMENT NO.		SHEET NO. 1 OF 1		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-84590-004			
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					