




LOC		DIST		REVISIONS						
AA		00		P	LTR	DESCRIPTION		DATE	DWN	APVD
					B	EC-06-024807		03NOV06	LAM	JW

D

C

B

A




- MATERIAL: HOUSING—HIGH TEMPERATURE NYLON, BLACK, IR COMPATIBLE, UL 94V-0.
TERMINALS — 0.33 [0.013] THICK PHOS BRONZE PLATED WITH 1.27μm [0.000050] MINIMUM HARD GOLD IN LOCALIZED AREA AND 3.81μm [0.000150] MINIMUM MATTE TIN IN SOLDER AREA OVER 1.27μm [0.000050] MINIMUM NICKEL UNDERPLATE

JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.

CAUTION: CATEGORY 5 JACK SOLDER TAIL POSITIONS DO NOT FOLLOW SAME NUMBER SEQUENCE AS THAT OF THE TRADITIONAL JACKS.



TRADITIONAL JACK CATEGORY 5 JACK



D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W. LONG/L.A.MAYER 03NOV2006	tyco Electronics		Tyco Electronics Corporation Harriaburg, PA 17105-3608	
		CHK J. WESTMAN 03NOV2006				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. FLICKINGER 03NOV2006	NAME		MODULAR JACK ASSEMBLY, 6 PORT, 8 POSITION, RIGHT ANGLE, CATEGORY 5	
		PRODUCT SPEC	108-1392			
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [010] 3 PLC ± - 4 PLC ± - ANGLES ± ± -	APPLICATION SPEC	114-2048			
		FINISH	SEE NOTE 1			
MATERIAL SEE NOTE 1		WEIGHT -	A1 00779		5558501	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1		REV B