


# DATA SHEET



**BC369**

PNP medium power transistor;  
20 V, 1 A

Product data sheet  
Supersedes data of 2003 Nov 20

2004 Nov 05

# PNP medium power transistor; 20 V, 1 A

**BC369****FEATURES**

- High current
- Two current gain selections.

**APPLICATIONS**

- Linear voltage regulators
- High side switches
- Supply line switches
- MOSFET drivers
- Audio pre-amplifiers.

**QUICK REFERENCE DATA**

SYMBOL	PARAMETER	MIN.	MAX.	UNIT
$V_{CEO}$	collector-emitter voltage	–	–20	V
$I_C$	collector current (DC)	–	–1	A
$I_{CM}$	peak collector current	–	–2	A
$h_{FE}$	DC current gain			
	BC369	85	375	
	BC369-16	100	250	
	BC369-25	160	375	


**DESCRIPTION**

PNP medium power transistor (see “Simplified outline, symbol and pinning”) for package details.

**PRODUCT OVERVIEW**

TYPE NUMBER	PACKAGE		MARKING CODE
	PHILIPS	EIAJ	
BC369	SOT54	SC-43A	C369
BC369-16	SOT54	SC-43A	C36916
BC369-25	SOT54	SC-43A	C36925

**SIMPLIFIED OUTLINE, SYMBOL AND PINNING**

TYPE NUMBER	SIMPLIFIED OUTLINE AND SYMBOL	PINNING	
		PIN	DESCRIPTION
BC369		1 2 3	base collector emitter

**ORDERING INFORMATION**

TYPE NUMBER	PACKAGE		
	NAME	DESCRIPTION	VERSION
BC369	SC-43A	plastic single-ended leaded (through hole) package; 3 leads	SOT54
BC369-16			
BC369-25			

# PNP medium power transistor; 20 V, 1 A

BC369

## LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC 60134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
$V_{CBO}$	collector-base voltage	open emitter	–	–32	V
$V_{CEO}$	collector-emitter voltage	open base	–	–20	V
$V_{EBO}$	emitter-base voltage	open collector	–	–5	V
$I_C$	collector current (DC)		–	–1	A
$I_{CM}$	peak collector current		–	–2	A
$I_{BM}$	peak base current		–	–200	mA
$P_{tot}$	total power dissipation	$T_{amb} \leq 25\text{ °C}$ ; notes 1 and 2	–	830	mW
$T_{stg}$	storage temperature		–65	+150	°C
$T_j$	junction temperature		–	150	°C
$T_{amb}$	ambient temperature		–65	+150	°C

## Notes

1. Refer to SOT54 (SC-43A) standard mounting conditions.
2. Device mounted on a FR4 printed-circuit board; single-sided copper; tin-plated; standard footprint for SOT54.




Fig.1 Power derating curve for standard PCB footprint.

PNP medium power transistor;  
20 V, 1 A


BC369

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
$R_{th(j-a)}$	thermal resistance from junction to ambient	$T_{amb} \leq 25\text{ }^{\circ}\text{C}$ ; notes 1 and 2	150	K/W

Notes

1. Refer to SOT54 (SC-43A) standard mounting conditions.
2. Device mounted on a FR4 printed-circuit board; single-sided copper; tin-plated; standard footprint for SOT54.



# PNP medium power transistor; 20 V, 1 A

BC369


## CHARACTERISTICS

$T_{amb} = 25\text{ °C}$  unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
$I_{CBO}$	collector-base cut-off current	$V_{CB} = -25\text{ V}; I_E = 0\text{ A}$	–	–	–100	nA
		$V_{CB} = -25\text{ V}; I_E = 0\text{ A}; T_J = 150\text{ °C}$	–	–	–10	$\mu\text{A}$
$I_{EBO}$	emitter-base cut-off current	$V_{EB} = -5\text{ V}; I_C = 0\text{ A}$	–	–	–100	nA
$h_{FE}$	DC current gain BC369	$V_{CE} = -10\text{ V}; I_C = -5\text{ mA}$	50	–	–	
		$V_{CE} = -1\text{ V}; I_C = -500\text{ mA}$	85	–	375	
		$V_{CE} = -1\text{ V}; I_C = -1\text{ A}$	60	–	–	
	BC369-16	$V_{CE} = -1\text{ V}; I_C = -500\text{ mA}$	100	–	250	
	BC369-25	$V_{CE} = -1\text{ V}; I_C = -500\text{ mA}$	160	–	375	
$V_{CEsat}$	collector-emitter saturation voltage	$I_C = -1\text{ A}; I_B = -100\text{ mA}$	–	–	–500	mV
$V_{BE}$	base-emitter voltage	$V_{CE} = -10\text{ V}; I_C = -5\text{ mA}$	–	–	–700	mV
		$V_{CE} = -1\text{ V}; I_C = -1\text{ A}$	–	–	–1	V
$C_c$	collector capacitance	$V_{CB} = -10\text{ V}; I_E = i_e = 0\text{ A}; f = 1\text{ MHz}$	–	28	–	pF
$f_T$	transition frequency	$V_{CE} = -5\text{ V}; I_C = -50\text{ mA}; f = 100\text{ MHz}$	40	140	–	MHz


# PNP medium power transistor; 20 V, 1 A

BC369

**BC369-16.** $T_{amb} = 25\text{ }^{\circ}\text{C}.$ 

- |                              |                              |
|------------------------------|------------------------------|
| (1) $I_B = -18\text{ mA}.$   | (6) $I_B = -9.0\text{ mA}.$  |
| (2) $I_B = -16.2\text{ mA}.$ | (7) $I_B = -7.2\text{ mA}.$  |
| (3) $I_B = -14.4\text{ mA}.$ | (8) $I_B = -5.4\text{ mA}.$  |
| (4) $I_B = -12.6\text{ mA}.$ | (9) $I_B = -3.6\text{ mA}.$  |
| (5) $I_B = -10.8\text{ mA}.$ | (10) $I_B = -1.8\text{ mA}.$ |



**Fig.3** Collector current as a function of collector-emitter voltage; typical values.

**BC369-16.** $V_{CE} = -1\text{ V}.$ 

**Fig.4** Base-emitter voltage as a function of collector current; typical values.


PNP medium power transistor;  
20 V, 1 A

BC369



# PNP medium power transistor; 20 V, 1 A

BC369

**BC369-25.** $T_{amb} = 25\text{ }^{\circ}\text{C}.$ 

- |                              |                              |
|------------------------------|------------------------------|
| (1) $I_B = -12\text{ mA}.$   | (6) $I_B = -6.0\text{ mA}.$  |
| (2) $I_B = -10.8\text{ mA}.$ | (7) $I_B = -4.8\text{ mA}.$  |
| (3) $I_B = -9.6\text{ mA}.$  | (8) $I_B = -3.6\text{ mA}.$  |
| (4) $I_B = -8.4\text{ mA}.$  | (9) $I_B = -2.4\text{ mA}.$  |
| (5) $I_B = -7.2\text{ mA}.$  | (10) $I_B = -1.2\text{ mA}.$ |

Fig.7 Collector current as a function of collector-emitter voltage; typical values.



**BC369-25.** $V_{CE} = -1\text{ V}.$ 

Fig.8 Base-emitter voltage as a function of collector current; typical values.



PNP medium power transistor;  
20 V, 1 A


BC369



BC369-25.

$V_{CE} = -1$  V.

Fig.9 DC current gain as a function of collector current; typical values.



BC369-25.

$I_C/I_B = 10$ .

Fig.10 Collector-emitter saturation voltage as a function of collector current; typical values.


PNP medium power transistor;  
20 V, 1 A

BC369

PACKAGE OUTLINE

Plastic single-ended leaded (through hole) package; 3 leads

SOT54



DIMENSIONS (mm are the original dimensions)

UNIT	A	b	b <sub>1</sub>	c	D	d	E	e	e <sub>1</sub>	L	L <sub>1</sub> <sup>(1)</sup> max.
mm	5.2 5.0	0.48 0.40	0.66 0.55	0.45 0.38	4.8 4.4	1.7 1.4	4.2 3.6	2.54	1.27	14.5 12.7	2.5

**Note**  
1. Terminal dimensions within this zone are uncontrolled to allow for flow of plastic and terminal irregularities.

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	JEITA			
SOT54		TO-92	SC-43A			04-06-28 04-11-16

# PNP medium power transistor; 20 V, 1 A

BC369

## DATA SHEET STATUS

DOCUMENT STATUS <sup>(1)</sup>	PRODUCT STATUS <sup>(2)</sup>	DEFINITION
Objective data sheet	Development	This document contains data from the objective specification for product development.
Preliminary data sheet	Qualification	This document contains data from the preliminary specification.
Product data sheet	Production	This document contains the product specification.

## Notes

1. Please consult the most recently issued document before initiating or completing a design.
2. The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nxp.com>.

## DISCLAIMERS

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions

above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

**Terms and conditions of sale** — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

# ***NXP Semiconductors***

## **Customer notification**

This data sheet was changed to reflect the new company name NXP Semiconductors, including new legal definitions and disclaimers. No changes were made to the technical content, except for package outline drawings which were updated to the latest version.

## **Contact information**

For additional information please visit: **<http://www.nxp.com>**

For sales offices addresses send e-mail to: **[salesaddresses@nxp.com](mailto:salesaddresses@nxp.com)**

© NXP B.V. 2009

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands

R75/05/pp12

Date of release: 2004 Nov 05

Document order number: 9397 750 13565

founded by

**PHILIPS**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NXP:](#)  
[BC369](#)