


FEATURES

- CLASS II DIELECTRIC, TEMPERATURE STABLE
- EXCELLENT FREQUENCY CHARACTERISTICS, NON-LINEAR CAPACITANCE CHANGE
- HIGHER CAPACITANCE THAN NPO
- NICKEL BARRIER TERMINATIONS AND EXCELLENT MECHANICAL STRENGTH






**RoHS
Compliant**

Includes all homogeneous materials

*See Part Number System for Details



Capacitance Range	47pF ~ 0.82μF (see high CV datasheet for higher capacitance values)
Capacitance Tolerance	±5% (J), ±10% (K), ±20% (M)
Operating Temperature Range	-55°C ~ +125°C
Temperature Characteristics	±15%Δ max. over temperature range (with 0 Vdc applied)
Rated Voltages	10Vdc, 16Vdc, 25Vdc, 35Vdc, 50Vdc (see NMC-H Series for higher voltages)
Dissipation Factor	2.5% max. (50Vdc, 100Vdc); 3.5% max. (16Vdc, 25Vdc) 5% max. (10Vdc) @ 1.0Vrms and 1KHz, +25°C
Insulation Resistance	10,000Megohms min. or 500Megohm/μF min. whichever is less @ +25°C
Dielectric Withstanding Voltage	250% of Rated Voltage for 5 ±1 seconds, 50mA maximum current
Test Conditions (EIA-198-2E)	1KHz, 1.0V ±0.2Vrms



PART NUMBER SYSTEM

NMC 0805 X7R 102 K 50 TRP or TRPLP 3K 7C3 E

NMC: Series
 0805: Size Code (see chart)
 X7R: Temperature Characteristic
 102: Capacitance Code, expressed in pF, first 2 digits are significant, 3rd digit is no. of zeros, "R" indicates decimal for under 10pF
 K: Capacitance Tolerance Code (see chart)
 50: Voltage (Vdc)
 TRP or TRPLP: Tape & Reel (Punched carrier)
 3K: Optional Reel Qty (3K=3,000pcs)
 7C3: Optional RoHS 7C-III Exemption Free*
 E: RoHS Compliant

* - Part Number Level Identification of X7R MLCCs that do not take RoHS exemption 7C-III




X7R CAPACITOR SIZE CHART (mm)

EIA Case Size	0201				0402				0603				0805					
Length (L)	0.6±0.03				1.0±0.05				1.6±0.15				2.0±0.2					
Width (W)	0.3±0.03				0.5±0.05				0.8±0.15				1.25±0.2					
Thickness max. (T)	0.3±0.03				0.6				1.0				1.35					
Termination Width (P)	0.15±0.05				0.2±0.1				0.12 ~ 0.51				0.25 ~ 0.71					
Capacitance	Working Voltage (Vdc)																	
	16	25	50	10	16	25	50	10	16	25	50	100	10	16	25	50	100	
47pF ~ 91pF																		
100pF ~ 470pF																		
510pF																		
560pF																		
620pF																		
680pF																		
750pF																		
820pF																		
910pF																		
0.001µF																		
0.0012µF																		
0.0015µF																		
0.0018µF																		
0.0022µF																		
0.0027µF																		
0.0030µF																		
0.0033µF																		
0.0039µF																		
0.0047µF																		
0.0056µF																		
0.0068µF																		
0.0075µF																		
0.0082µF																		
0.01µF																		
0.012µF																		
0.015µF																		
0.018µF																		
0.022µF																		
0.033µF																		
0.039µF																		
0.047µF																		
0.056µF																		
0.068µF																		
0.082µF																		
0.1µF																	*	
0.15µF														*	*	*		
0.18µF														*	*	*		
0.22µF														*	*	*		
0.33µF														*	*	*		
0.39µF														*	*	*	*	
0.47µF														*	*	*	*	
0.56µF														*	*	*		
0.68µF														*	*	*		
0.82µF														*	*	*		

*1.45mm maximum thickness

See NMC High CV series for values above 0.82µF



(CONSULT FACTORY
FOR CAPACITANCE
VALUES NOT LISTED)





X7R CAPACITOR SIZE CHART (mm)

EIA Case Size	1206					1210					1812					2225				
Length (L)	3.2±0.2					3.2±0.2					4.5±0.3					5.7±0.4				
Width (W)	1.6±0.2					2.5±0.2					3.2±0.25					6.35±0.25				
Thickness max. (T)	1.80					1.80					1.8					1.80				
Termination Width (P)	0.25 ~ 0.71					0.25~0.75					0.25 ~ 0.75					0.25 ~ 1.02				
Capacitance	Working Voltage (Vdc)																			
	10	16	25	50	100	10	16	25	35	50	100	10	16	25	50	100	25	50	100	
150pF ~ 910pF																				
0.001																				
0.0012μF																				
0.0015μF																				
0.0018μF																				
0.0022μF																				
0.0027μF																				
0.0033μF																				
0.0036μF																				
0.0039μF																				
0.0043μF																				
0.0047μF																				
0.0056μF																				
0.0068μF																				
0.0075μF																				
0.0082μF																				
0.01μF																				
0.012μF																				
0.015μF																				
0.018μF																				
0.022μF																				
0.027μF																				
0.033μF																				
0.036μF																				
0.039μF																				
0.043μF																				
0.047μF																				
0.056μF																				
0.068μF																				
0.082μF																				
0.1μF																				
0.12μF																				
0.15μF																				
0.18μF																				
0.22μF																				
0.27μF																				
0.33μF																				
0.39μF																				
0.47μF																				
0.56μF																				
0.68μF																				
0.82μF															*	*				

* 2.20mm maximum thickness

See NMC High CV series for values above 0.82μF





REEL DIMENSIONS (mm)

Reel Diameter (A)	B	C	D	T max.
7" (178 ± 2.0)	13 ± 0.5	50 min.	21 ± 1.0	8.4 +1.0/-0 (1812 case size 12.4 +2.0/-0)
10" (250 ± 2.0)		100 ± 1.0		
13" (330 ± 2.0)		100 ± 1.0		

7 INCH REEL QUANTITIES*

Size	01005	0201	0402	0603	0805	1206	1210	1812
Tape Size	8mm	8mm	8mm	8mm	8mm	8mm	8mm	12mm
Min. Qty Per Reel	20,000	20,000	10,000	4,000	4,000	4,000	2,000	1,000
Max. Qty Per Reel	20,000	20,000	10,000	4,000	5,000	5,000	5,000	2,000

*Quantity dependent on chip thickness. Contact NIC for reel quantities on larger diameter reels.

CARRIER TAPE MATERIAL

Parts with a thickness of ≥1mm will be taped on embossed plastic carrier. Parts with a thickness of less than 1mm will be taped on paper carrier


EMBOSSED PLASTIC CARRIER TAPE DIMENSIONS (mm)

Tape Size	W	F	E	P ₀	P ₂	D	K max.	T max.	P
8mm	8.0 ± 0.2	3.5 ± 0.05	1.75 ± 0.10	4.0 ± 0.1	2.0 ± 0.5	1.5 ^{+0.1} _{-0.0}	3.0	2.0	4.0 ± 0.1
12mm	12 ± 0.2	5.5 ± 0.05						4.5	8.0 ± 0.1

Notes:

- Specifications are in compliance with EIA RS481-1-A "Taping of surface Mount Components for Automatic Placement"
- Dimensions A₀ (max.) equals component width dimension plus 0.5mm
- Dimension B₀ (max.) equals component length dimension plus 0.5mm

EMBOSSED PLASTIC CARRIER TAPE



See notes 2 & 3 regarding dimensions A₀ and B₀

PUNCHED CARRIER TAPE DIMENSIONS (mm)

Type	A ₀	B ₀	W	F	E	P1	P0	D0	T1 max.	T2 max.	Mounting Hole			
01005	0.25 ± 0.04	0.45 ± 0.04	8.0 ± 0.3	3.5 ± 0.05	1.75 ± 0.1	2.0 ± 0.05	4.0 ± 0.1	1.5 +0.1/-0.0	0.27	0.36	Angular Punch Hole			
0201	0.37 ± 0.03	0.67 ± 0.05							0.45	0.80				
0402	0.65 ± 0.05	1.15 ± 0.05				4.0 ± 0.10			1.1	1.4				
0603	1.1 ± 0.2	1.9 ± 0.2												
0805	1.65 ± 0.2	2.4 ± 0.2												
1206	2.0 ± 0.2	3.6 ± 0.2												

PUNCHED CARRIER TAPE

