




- VDC: 5, 12
- RPM: 1800~6200
- CFM: 3.31~12.35
- Impeller: 7 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 26; UL 1007 lead wires
- Mass: 21g



DC FAN

50x50x11mm


Specification

	Bearing	Voltage	Current	Speed	Input Power	Air Flow	Static Pressure	Noise	Weight
MODEL NO	○ Sleeve ● One ball and one sleeve ○ Hydraulic	(Vdc)	(Amp)	(Rpm)	(Watts)	(CFM)	(mm/H ₂ O)	dB(A)	Gram
B5010B05E	●	5	0.10	3500	0.50	6.90	1.72	24.5	21
B5010S05E	○	5	0.10	3300	0.50	6.34	1.30	23.4	21
B5010B05L	●	5	0.14	4200	0.70	8.21	2.17	28.3	21
B5010S05L	○	5	0.14	4000	0.70	6.98	1.75	26.4	21
B5010B05M	●	5	0.15	5200	0.75	10.24	3.25	35.1	21
B5010B05H	●	5	0.15	6200	0.75	12.35	4.31	38.1	21
B5010B12E	●	12	0.05	3500	0.60	6.90	1.72	24.5	21
B5010S12E	○	12	0.05	3300	0.60	6.34	1.30	23.4	21
B5010B12L	●	12	0.07	4200	0.84	8.21	2.17	28.3	21
B5010S12L	○	12	0.07	4000	0.84	6.98	1.75	26.4	21
B5010B12M	●	12	0.10	5200	1.20	10.24	3.25	35.1	21
B5010B12H	●	12	0.15	6200	1.80	12.35	4.31	38.1	21
C5010B05E	●	5	0.10	3500	0.50	6.90	1.72	24.5	21
C5010B05L	●	5	0.16	4200	0.80	8.21	2.17	28.3	21
C5010B05M	●	5	0.18	5200	0.90	10.24	3.25	35.1	21
C5010B12E	●	12	0.05	3500	0.60	6.90	1.72	24.5	21
C5010S12E	○	12	0.05	3300	0.60	6.34	1.30	23.4	21
C5010B12L	●	12	0.07	4200	0.84	8.21	2.17	28.3	21
C5010A12L	●	12	0.07	4200	0.84	8.21	2.17	28.3	21
C5010S12L	○	12	0.07	4000	0.84	6.98	1.75	26.4	21
C5010B12M	●	12	0.10	5200	1.20	10.24	3.25	35.1	21
C5010A12M	●	12	0.10	5200	1.20	10.24	3.25	35.1	21
C5010B12H	●	12	0.15	6200	1.80	12.35	4.31	38.1	21
C5010A12H	●	12	0.15	6200	1.80	12.35	4.31	38.1	21
D5010B05L	●	5	0.16	4200	0.80	8.21	2.17	28.3	21
D5010B05M	●	5	0.18	5200	0.90	10.24	3.25	35.1	21
D5010B12E	●	12	0.05	3500	0.60	6.90	1.72	24.5	21
D5010S12E	○	12	0.05	3300	0.60	6.34	1.30	23.4	21
D5010B12L	●	12	0.07	4200	0.84	8.21	2.17	28.3	21
D5010A12L	●	12	0.08	4200	0.96	8.21	2.17	28.3	21
D5010S12L	○	12	0.07	4000	0.84	6.98	1.75	26.4	21
D5010B12M	●	12	0.10	5200	1.20	10.24	3.25	35.1	21
D5010B12H	●	12	0.15	6200	1.80	12.35	4.31	38.1	21
E5010B12M	●	12	0.07~0.23	1800~5200	0.84~2.76	3.31~10.24	0.49~3.25	21.0~35.1	21
F5010B05E	●	5	0.10	3500	0.50	6.90	1.72	24.5	21
F5010S05E	○	5	0.10	3300	0.50	6.34	1.30	23.4	21
F5010B05L	●	5	0.13	4200	0.65	8.21	2.17	28.3	21
F5010S05L	○	5	0.13	4000	0.65	6.98	1.75	26.4	21
F5010B05M	●	5	0.22	5200	1.10	10.24	3.25	35.1	21
F5010B05H	●	5	0.32	6200	1.60	12.35	4.31	38.1	21
F5010B12E	●	12	0.05	3500	0.60	6.90	1.72	24.5	21
F5010B12L	●	12	0.07	4200	0.84	8.21	2.17	28.3	21
F5010S12L	○	12	0.07	4000	0.84	6.98	1.75	26.4	21
F5010B12M	●	12	0.10	5200	1.20	10.24	3.25	35.1	21
F5010B12H	●	12	0.14	6200	1.68	12.35	4.31	38.1	21

Design specifics subject to change without notice.




- VDC: 5, 12
- RPM: 1800~6200
- CFM: 3.31~12.35
- Impeller: 7 blades
- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 26; UL 1007 lead wires
- Mass: 21g



DC FAN

50x50x11mm



STATIC PRESSURE

