

## main menu



home  
 test & measurement  
 products  
 skills  
 download

## online catalogue T&amp;M

clamp-type test probes  
 crocodile clips  
 test probes  
 oscilloscope test probes  
 measuring leads  
 plugs  
 sockets  
 ▶ 2 mm system  
 ▶ 2 mm safety system  
 ▶ 4 mm system  
 ▶ 4 mm safety system

## sets

miscellaneous

## company

portrait  
 corporate association  
 location maps  
 fairs and exhibitions  
 jobs  
 imprint  
 terms and conditions

Home ▶ sockets ▶ sockets ▶ KUN S

## KUN S

datasheet for KUN S  
 article number: 934096103



View Full-Size Image



## search online catalogue

Search

Search

## Messetermine

No events

## QR-Code



|                                                |                                                                                                                                                                                                                                                        |
|------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>product description:</b>                    | order number: 934 096-103                                                                                                                                                                                                                              |
| <b>description:</b>                            | Safety coupling with screw connection for leads from 0.5mm <sup>2</sup> to 1.5mm <sup>2</sup> , outer diameter of lead max. 4,2mm<br>Connectable with plugs 4mm and safety plugs 4mm<br>1000V-system, IEC 61010.<br>Simple assembly by "Click-System". |
| <b>typ:</b>                                    | KUN S gelb/yellow                                                                                                                                                                                                                                      |
| <b>system:</b>                                 | 4 mm safety system                                                                                                                                                                                                                                     |
| <b>order number:</b>                           | 934 096-103                                                                                                                                                                                                                                            |
| <b>color</b>                                   |                                                                                                                                                                                                                                                        |
| <b>other color versions:</b>                   |                                                                                                                                                                                                                                                        |
| <b>technical data</b>                          |                                                                                                                                                                                                                                                        |
| <b>measurement category acc. to IEC 61010:</b> | CAT III                                                                                                                                                                                                                                                |
| <b>type of contact:</b>                        | unsprung socket Ø 4 mm                                                                                                                                                                                                                                 |
| <b>type of termination:</b>                    | screw                                                                                                                                                                                                                                                  |
| <b>rated voltage:</b>                          | AC/DC 1000 V                                                                                                                                                                                                                                           |
| <b>rated current:</b>                          | 24 A                                                                                                                                                                                                                                                   |
| <b>Please consider derating curve!</b>         |                                                                                                                                                                                                                                                        |
| <b>material</b>                                |                                                                                                                                                                                                                                                        |
| <b>contact material:</b>                       | brass                                                                                                                                                                                                                                                  |
| <b>contact surface material:</b>               | nickel                                                                                                                                                                                                                                                 |
| <b>housing material:</b>                       | PA                                                                                                                                                                                                                                                     |
| <b>environmental conditions:</b>               |                                                                                                                                                                                                                                                        |
| <b>temperature range:</b>                      | -15 °C to +70 °C                                                                                                                                                                                                                                       |
| <b>flammable class:</b>                        |                                                                                                                                                                                                                                                        |
| <b>housing (basic material):</b>               | UL 94 V - 2                                                                                                                                                                                                                                            |
| <b>drawing</b>                                 |                                                                                                                                                                                                                                                        |

