

Datasheet for part number 121584-0017

Our Catalog Part Number: DANGZ-15P-P1
Our Global Manufacturing Part Number: 121584-0017
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*NG

Product Datasheet	
General	Straight Pressfit Connector
Mating Cycles	50
Dielectric Withstanding Voltage	1200 VAC at sea level
Current Rating	5 A at 25°C 3.5 A at 70°C
Contact Resistance	10 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	steel
Shell Finish	tin
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Contact Arrangement	15 contacts size 20
Gender	Pin
Contact Type	stamped
Contact Material	copper alloy
Contact Finish	gold flash (Performance Class 3)
Contact Termination	Right angled solder
Mounting Methode	.300" (7.6mm) 4-40 Standoff, Boardlock