




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- TUSONIX STANDARD PART NUMBER: 4206-006.
TUSONIX RoHS COMPLIANT PART NUMBER: 4206-006 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- LEAD FINISH: STANDARD PART #: SILVER PLATED WITH 60/40 SOLDER DIP. RoHS PART #: SILVER PLATED WITH 95.5 Sn/3.8 Ag/0.7 Cu SOLDER DIP.
- PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
- SUPPLIED WITH SILVER PLATED HEX NUT AND INTERNAL TOOTH LOCK WASHER.

CAP. (pF)	WORKING VOLTAGE DC (V)		CURRENT dc (A)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	85 °C	125 °C		10 MHz	100 MHz	1 GHz	10 GHz
3000 MIN.	1000	500	25 A	10	55	70	70

X-2015 Rev-0	REVISION RECORD		TOLERANCES unless otherwise specified		Title EMI LOW PASS FILTER	
	Original Release	0	2 PLC. DECIMAL ±			
	DIM. 562 WAS .567, SM 12-5-97	6	3 PLC. DECIMAL ± .031 [0.79]		Drawn	E.C. 06-07-96
	NOTE REVISED & DELETED VAR. S.M. 06-08-99	7	ANGLES ±		Scale	2 X
ADDED NOTES 1-3 & CIRCUIT. S.M. 07-29-05		8	TUSONIX TUCSON, ARIZONA		Approved B.Mc. 06-07-96	
20050727-3-02					A	4206-006