

TG/LTG-Series



The TG-Series Mini Tippette rocker switches are single or double pole and feature an all nylon double-insulated construction. These switches are designed with snap-in mounting for fast, low cost assembly. The illuminated version (LTG) is available with either a paddle or rocker actuator. These AC rated switches are also suitable for low-voltage DC applications.

- Specifications
- Certifications*: UL, CSA, VDE
 - Dielectric Strength: 1,000 V (minimum)
 - Insulation Resistance: 100 Megohms (minimum)
 - Base Material: Nylon
 - Actuator Material: Nylon or Polycarbonate
 - Bezel Material: Nylon


* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



LTG		G	O	50	1	-	T	B	-	B	-	R	/	125N													
SERIES		RATING			ACTUATOR STYLE		ACTUATOR COLOR ²		BASE COLOR ²																		
TG	DOUBLE POLE	40	5A 250VAC	10A 125VAC	P	PADDLE	B	BLACK	B	BLACK																	
	NON-LIGHTED																										
LTG	DOUBLE POLE	41	5A 250VAC	10A 125VAC	T	ROCKER	W	WHITE	W	WHITE																	
	W/INDICATOR LIGHTS																										
CIRCUIT ¹		50			TERMINATION/FUNCTION				LENS COLOR ³																		
See Circuit Designation Chart Page 39		50	10A 250VAC	15A 125VAC																							
CENTER POSITION									LAMP VOLTAGE																		
C CENTER OFF		51	10A 250VAC	15A 125VAC																							
O NO CENTER OFF																											

Circuit Designation Chart - refers to TG/LTG, TTG and TLG-Series Switches pages 36-38



● CONTACT TERMINAL
Will make contact with switching lever

● CONTACT TERMINAL AND SWITCH LEVER

○ ISOLATED TERMINAL
Does not make contact with switching lever

⊗ BULB

NOTES:
For variations to above circuits, consult factory.