







E	5	35.56 [1.400]	14	37.69 [1.484]	30	6-146130-4	
	5	33.02 [1.300]	13	35.15 [1.384]	28	6-146130-3	
E	5	30.48 [1.200]	12	32.61 [1.284]	26	6-146130-2	
	5	27.94 [1.100]	11	30.07 [1.184]	24	6-146130-1	
	5	25.40 [1.000]	10	27.53 [1.084]	22	6-146130-0	
	5	22.86 [.900]	9	24.99 [.984]	20	5-146130-9	
	5	20.32 [.800]	8	22.45 [.884]	18	5-146130-8	
	5	17.78 [.700]	7	19.91 [.784]	16	5-146130-7	
	5	15.24 [.600]	6	17.37 [.684]	14	5-146130-6	
	5	12.70 [.500]	5	14.83 [.584]	12	5-146130-5	
	5	10.16 [.400]	4	12.29 [.484]	10	5-146130-4	
	5	7.62 [.300]	3	9.75 [.384]	8	5-146130-3	
	5	5.08 [.200]	2	7.21 [.284]	6	5-146130-2	
	5	2.54 [.100]	1	4.67 [.184]	4	5-146130-1	
	E	5	17.78 [.700]	7	19.91 [.784]	16	1-146130-8
	E	5	5.08 [.200]	2	7.21 [.284]	6	1-146130-7
	E	3	35.56 [1.400]	14	37.69 [1.484]	30	1-146130-4
3		33.02 [1.300]	13	35.15 [1.384]	28	1-146130-3	
D	3	30.48 [1.200]	12	32.61 [1.284]	26	1-146130-2	
	3	27.94 [1.100]	11	30.07 [1.184]	24	1-146130-1	
	3	25.40 [1.000]	10	27.53 [1.084]	22	1-146130-0	
D	3	22.86 [.900]	9	24.99 [.984]	20	146130-9	
	3	20.32 [.800]	8	22.45 [.884]	18	146130-8	
	3	17.78 [.700]	7	19.91 [.784]	16	146130-7	
	3	15.24 [.600]	6	17.37 [.684]	14	146130-6	
	3	12.70 [.500]	5	14.83 [.584]	12	146130-5	
	3	10.16 [.400]	4	12.29 [.484]	10	146130-4	
	3	7.62 [.300]	3	9.75 [.384]	8	146130-3	
	3	5.08 [.200]	2	7.21 [.284]	6	146130-2	
	3	2.54 [.100]	1	4.67 [.184]	4	146130-1	
	PLATING	C	B	A	NO OF POSN	PART NUMBER	



RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.KNAUB	30-09-94				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	G DUBNICZKI	30-09-94			
	0 PCL ± -	NAME	APVD G DUBNICZKI	30-09-94	SURFACE MOUNT HEADER ASSEMBLY, MOD II, BREAKAWAY, VERTICAL, DOUBLE ROW, .100 X.100 CL, .025 SQ.POST		
	1 PCL ± -		PRODUCT SPEC				
	3 PCL ± 0.13(.005)		APPLICATION SPEC				
	4 PCL ± -						
	ANGLES						
	SEE TABLE						
MATERIAL	FINISH	WEIGHT	—	A1	00779 C=146130	RESTRICTED TO	
	CUSTOMER DRAWING	SHEET	R-1	OF	1	REV	—