



DESCRIPTION: .625 CENTER DUAL PORT D-SUB MALE/FEMALE

	A	B	C
9	1.204	.984	.494
	30.6	25.0	12.55
15	1.535	1.312	.494
	39.0	33.3	12.55
25	2.078	1.850	.494
	52.8	47.0	12.55
37	2.724	2.500	.494
	69.2	63.5	12.55



189-XXX-412-571

SERIES _____
POSITIONS _____

009
015
025
037

GENDER _____
61 = MALE OVER MALE
41 = MALE OVER FEMALE
51 = FEMALE OVER FEMALE
31 = FEMALE OVER MALE

SHELL PLATING _____
2 = TIN
HARDWARE OPTIONS _____
57 = 4-40 STANDOFFS/FORK BOARD LOCKS
PLATING OPTIONS _____
01 = GOLD FLASH

SPECIFICATIONS:
MATERIALS:
SHELL: STEEL, TIN PLATED
INSULATOR: UL 94V-0 RATED BLACK
GLASS-FILLED POLYESTER

ELECTRICALS:
CURRENT RATING: 5 AMPS
DIELECTRIC STRENGTH: 1000V AC RMS
INSULATOR RESISTANCE: 1000 MOHMS MIN
TEMPERATURE: -55°C TO +105°C



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: PAM JENKINS		DATE: 9-24-98	
CHECKED:		DATE:	
SCALE: 1:1	SHEET 1 OF 1	REV 5	
DWG NO. 189-XXX-412-571			