





D

C

B


A



1. RECOMMENDED MOUNTING HOLE PATTERN FOR .109±0.016 THICK P.C.BOARD 2.

.060	1.52	-	-
.051	1.30	1.716	43.59
.046	1.17	.750	19.05
.045	1.14	.450	11.43
.030	0.76	.425	10.80
.017	0.43	.312	7.92
.015	0.38	.300	7.62
.012	0.30	.180	4.57
.010	0.25	.175	4.45
.008	0.20	.156	3.96
.005	0.13	.125	3.18
.003	0.08	.078	1.98
.001	0.03	.073	1.85
.000	0.00	.063	1.60
IN	MM	IN	MM
CONVERSION TABLE			

644741-1 SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN L. SMITH 04MAR94	 TE Connectivity					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK R. SWING 04MAR94	NAME D. CLARK 10MAR94	MTA-156 HEADER ASSEMBLY, FRICTION LOCK, STRAIGHT .045 ROUND POST, TIN PLATED, 11 POSITION, OMITTED POST				
		0. PLC ± .005 1. PLC ± .005 2. PLC ± .005 3. PLC ± .005 4. PLC ± .005 ANGLES ± .005		PRODUCT SPEC						
				APPLICATION SPEC						
				SIZE						
				CAGE CODE						
				DRAWING NO.						
				RESTRICTED TO						
MATERIAL		FINISH		WEIGHT						
				A1 00779 C644741						
CUSTOMER DRAWING				SCALE 5:1						SHEET 1 OF 1