



### TYPICAL PASSBAND CHARACTERISTIC



### DIMENSION



### SPECIFICATION

| Application         | DECT                                                         |                      |      |      |          |
|---------------------|--------------------------------------------------------------|----------------------|------|------|----------|
|                     | SYMBOL                                                       | Min                  | Typ. | Max. | Unit     |
| Center Frequency    | $f_o$                                                        |                      | 1890 |      | MHz      |
| Bandwidth           | BW                                                           | $f_o \pm 10$         |      |      | MHz      |
| Insertion Loss      | IL                                                           |                      |      | 2.0  | dB       |
| Ripple              |                                                              |                      |      | 0.5  | dB       |
| Standing Wave Ratio | VSWR                                                         |                      |      | 2.0  |          |
| Impedance           | Z                                                            |                      | 50   |      | $\Omega$ |
| Attenuation         | 1660~1680MHz<br>1770~1790MHz<br>3760~3800MHz<br>5640~5700MHz | 45<br>15<br>35<br>10 |      |      | dB       |