


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		D1	REVISED PER ECO-15-013426	18SEP2015	NK	DR

AMP
WIRE RANGE

22-16 AWG
SOLID OR STRANDED



- 1
- STAMP AMP 22-18* APPROX AS SHOWN
-
- 22-16 TERMINALS ARE STAMPED 22-18 IN
-
- ACCORDANCE WITH MILITARY SPEC SAE AS7928
-
- COMMERCIAL WIRE RANGE IS 22-16

2

3

4

5

6

7

8

9

10

76	100	170°C MAX	LOOSE PIECE, BOX	2	8-34114-1
876	5000	170°C MAX	34114 ON TAPE	2	2-34114-2
	1000	343°C MAX	LOOSE PIECE	5	34114-4
	1000	170°C MAX	LOOSE PIECE	4	10 34114-3
	1000	260°C MAX	LOOSE PIECE	3	34114-1
876	1000	170°C MAX	LOOSE PIECE	2	34114
	QTY	MAX TEMP.	PACKAGE TYPE	FINISH	PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-10-93	 TE Connectivity											
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 	DWN DA PATTERSON 3-10-93	NAME TERMINAL, RING TONGUE, SOLISTRAND —											
	FOR APPLICATION	TOOLING ASSISTANCE CENTER	CIRCULAR MIL AREA: 0.26-1.65mm² [509-3260] CIR MILS SOLID OR STRANDED															
TOOLING INFORMATION	1-800-722-1111			MATERIAL 	FINISH SEE TABLE	APVD DE MILLER 3-10-93	PRODUCT SPEC —		APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO					
								WEIGHT —	A2 00779  34114				—					
FOR ORDER ENTRY	1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.															
CUSTOMER DRAWING							SCALE		8:1		SHEET		1 OF 1		REV		D1	