


DIMENSIONS IN INCHES. DO NOT SCALE PRINT.		MATL		HT TR		FIN	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		OR 230CT03 APP		270CT03 T.ELBIN		 AMP Incorporated Harrisburg, PA 17105-3608	
2 PLC DEC ±		CHK 230CT03		REL -			
2 PLC DEC ±		R.O. WILSON					
2 PLC DEC ±		NAME SIDE FEED HDM APPLICATOR					
2 PLC DEC ±		SCALE -					
2 PLC DEC ±		DWS NO 1385658					
2 PLC DEC ±		SHEET 1 OF 1					
2 PLC DEC ±		REV A					
2 PLC DEC ±		CAGE CODE 00779					
2 PLC DEC ±		CUSTOMER AND ASSEMBLY DRAWING					
2 PLC DEC ±		RESTRICTED TO					



								129
								128
2	2	2	-	C	5-354779-6	PIN, WIRE DISC (.3270)B		127
2	2	2	-	C	5-354779-0	PIN, WIRE DISC (.3240)A		126
1	1	1	-	A	986950-1	WASHER, FLAT PRECISION		125
REF	REF	REF	-	A	21045-3	RING,RET "C"(ø.187)FD FING PIN		124
								123
REF	REF	REF	-	A	5-21028-1	PIN,SLT SPR(ø.125x.50)ADJ ROD		122
1	1	1	-	A	4-21028-0	PIN,SLT SPR(ø.093x.75)ST GDE PL		121
REF	REF	REF	-	A	1-21030-1	PIN,DOWEL(ø.187x.50)LEVER		120
REF	REF	REF	-	A	1-21030-6	PIN,DOWEL(ø.187x1.25)HOUSING		119
								118
1	2	1	-	A	21024-5	WASHER, LOCK(#10)ADJ BLOCK		117
REF	REF	REF	-	A	21024-5	WASHER,LOCK(#10)ADJ PLATE		116
REF	REF	REF	-	A	21024-5	WASHER,LOCK(#10)FEED GDE ROD		115
2	2	2	-	A	21024-2	WASHER,LOCK(#4)FRONT STP GUIDE		114
								113
								112
4	4	4	-	A	21024-4	WASHER,LOCK(#8)STRIPPER		111
REF	REF	REF	-	A	21899-4	WASHER,FLAT(ø5/16)SCREW ADJ		110
-	1	REF	-	A	21899-2	WASHER,FLAT(NO.10)LUB ASSY		109
								108
REF	REF	REF	-	A	21018-5	NUT, HEX(6-32)FEED ADJ		107
								106
								105
1	1	-	-	A	992031-1	PIN, CLEVIS		104
1	1	1	-	A	21009-2	SCR,SKT SET(1/4-20x.25 LW)RAM		103
2	2	2	-	A	21017-2	SCR,DRIVE(#2x.19 ID)PLATE		102
REF	REF	REF	-	A	6-23715-5	SCR,PAN HD(6-32x1.50)FEED ADJ		101
1	1	1	-	B	461264-1	PLATE, IDENTIFICATION		100
2	2	2	-	A	3-21002-0	SCR,BHC(10-32x.88)DRAG		99
1	1	1	-	A	22733-8	SCR,BHC(8-32x.38 LW)ANVIL		98
REF	REF	REF	-	A	2-21002-9	SCR,BHC(10-32x.75)CAP		97
REF	REF	REF	-	A	2-22733-8	SCR,BHC(1/4-20x.62)HOUSING		96
REF	REF	REF	-	A	2-21002-7	SCR,BHC(10-32x.50)SG ADJ BLOCK		95
4	4	4	-	A	2-21002-2	SCR,BHC(8-32x.50)SHEAR		94
								93
2	2	2	-	A	1-21002-6	SCR,BHC(6-32x.25)TERM HOLD		92
1	1	1	-	A	1-21002-7	SCR,BHC(6-32x.38)CAM		91
								90
1	1	-	-	A	7-21000-9	SCR,SHC(4-40x.19)STRIPPER		89
								88
2	2	2	-	A	3-21000-0	SCR,SHC(8-32x.81)DEP-HOLD		87
1	1	1	-	A	2-22603-0	SCR,HEX HD(8-32x.31)FEED FINGER		86
2	2	2	-	A	1-21000-3	SCR,SHC(4-40x.25)F ST GUIDE		85
1	1	1	-	A	2-21000-7	SCR,SHC(8-32x.50)STRIPPER		84
REF	REF	REF	-	A	3-21000-7	SCR,SHC(10-32x.75)FEED ROD GD		83
REF	REF	REF	-	A	3-21000-6	SCR,SHC(10-32x.62)FD ADJ BLK		82
1	2	1	-	A	3-21000-4	SCR,SHC(10-32x.38)SG ADJ BL		81
REF	REF	REF	-	A	3-21000-4	SCR,SHC(10-32x.38)PIVOT BLK		80
-	REF	-	-	B	455749-1	GUARD, WINDOW		79
REF	-	-	-	B	679532-1	INSERT, GUARD		78
-	1	REF	-	C	1-465184-0	LUBRICATOR ASSY		77
								76
								75
1	1	1	-	A	690603-1	SPRING, ASSIST		74
1	1	1	-	A	23030-1	SCR,SHC(6-32x.25 SL)INS DISC		73
REF	REF	REF	-	A	458109-1	WASHER, SPECIAL		72
REF	REF	REF	-	A	690517-1	SPACER,		71
-3	-2	-1						
			U/M	DWG SIZE	PART NO	DESCRIPTION	ITEM NO	
				←	REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)			
QTY REQD PER ASSY				PARTS LIST				