

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.


LOC
HBDIST
-

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
C		REMOVED CSA&OPTIMIZATION SSA RATING&USING WELDED CONTACT ECO-14-003061	13Mar2014	HYS	B.F

PART A

PART B



C:MADE IN CHINA



CONNECTION FIGURE



FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)

Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
Fu.BoCHK
XN.ZhangAPVD
CH.HSUPRODUCT SPEC
SEE PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME

OJE-SH-LMH.SPEC.000

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1721875

SCALE 5:1

SHEET 1 OF 2

REV C

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC
HBDIST
-

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

- SEE SHEET 1

-

-

-

1721875-6	OJE-SH-124LMH-WG	24V	OJE-SH-124LMH-WG	f
1721875-5	OJE-SH-112LMH-WG	12V	OJE-SH-112LMH-WG	e
1721875-4	OJE-SH-109LMH-WG	9V	OJE-SH-109LMH-WG	d
1721875-3	OJE-SH-106LMH-WG	6V	OJE-SH-106LMH-WG	c
1721875-2	OJE-SH-105LMH-WG	5V	OJE-SH-105LMH-WG	b
1721875-1	OJE-SH-103LMH-WG	3V	OJE-SH-103LMH-WG	a
TE PART NO	DESCRIPTION	PART B	PART A	TYPE

RELAY TYPE

② NOTES:

1.LOT NO. SYSTEM AS FOLLOWING: ②5.ADD LOT NO. SYSTEM AS FOLLOWING;

WEEK
YEAR

1

1

A

I

II

III

I, DIGITS FOR DAY OF THE WEEK

1...MONDAY IN THIS WEEK;

2...TUESDAY IN THIS WEEK;

.....

7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;

2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE LINE
IDENTITY,

SUCH AS: A,B.....Z

②2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

②3.FOR THE TIN-PLATING OF THE PINS:

+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.

+0.5mm FOR LENGTH.

②④4.MARKING FROM INK TO LASER AND USING WELDED CONTACT

		UV RESIN	SEAL (VENT HOLE)	16
		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		MW79	MAGNETIC WIRE	14
94V-0		NYLON	CASE	13
94V-0		P.E.T	BASE	12
94V-0		NYLON	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		P.P.S	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag ALLOY	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
Fu.BoCHK
XN.ZhangAPVD
CH.HSU

PRODUCT SPEC

SEE PRODUCT SPEC

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME:

OJE-SH-LMH.SPEC.000

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1721875

SCALE 5:1

SHEET 2 OF 2

REV C