

Trunk line branch terminal - UDB 2X35/25 BN - 3071352

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Trunk line branch terminal, nom. voltage: 400 V, nominal current: 125 A, connection method: Screw connection, Screw connection, number of connections: 4, number of positions: 1, cross section: 10 mm² - 35 mm², AWG: 8 - 2, width: 27 mm, color: brown, mounting type: NS 35/7,5, NS 35/15

Why buy this product

- The branch terminal is suitable for the simple voltage pick-off of main supply cables
- Conformance with DIN VDE 0603-2/EN 60998-1

 RoHS

Key Commercial Data

Packing unit	5 STK
GTIN	 4 046356 735971
GTIN	4046356735971

Technical data

General

Number of positions	1
Number of levels	1
Number of connections	4
Potentials	1
Nominal cross section	35 mm ²
Color	brown
Insulating material	PA
Flammability rating according to UL 94	V0
Rated surge voltage	8 kV
Degree of pollution	3
Overvoltage category	III
Insulating material group	I
Maximum power dissipation for nominal condition	4.06 W
Maximum load current	125 A

Trunk line branch terminal - UDB 2X35/25 BN - 3071352

Technical data

General

Nominal current I_N	125 A
Nominal voltage U_N	400 V (max. 1000 V)
Open side panel	No

Dimensions

Width	27 mm
Length	55 mm
Height NS 35/7,5	46 mm
Height NS 35/15	53.5 mm

Connection data

Connection method	Screw connection
Connection in acc. with standard	IEC 60998-1
Note	Use ferrules for stranded conductors
Conductor cross section solid min.	10 mm ²
Conductor cross section solid max.	35 mm ²
Conductor cross section AWG min.	8
Conductor cross section AWG max.	2
Conductor cross section flexible min.	10 mm ²
Conductor cross section flexible max.	25 mm ²
Min. AWG conductor cross section, flexible	8
Max. AWG conductor cross section, flexible	3
Conductor cross section flexible, with ferrule without plastic sleeve min.	10 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	25 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	10 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	16 mm ²
Stripping length	25 mm
Screw thread	M6/M8
Tightening torque max	4 Nm
Connection method	Screw connection
Connection in acc. with standard	IEC 60998-1
Conductor cross section solid min.	1.5 mm ²
Conductor cross section solid max.	25 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve min.	1.5 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	16 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	1.5 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	10 mm ²
Stripping length	25 mm

Standards and Regulations

Connection in acc. with standard	IEC 60998-1
	IEC 60998-1

Trunk line branch terminal - UDB 2X35/25 BN - 3071352

Technical data

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Circuit diagram



Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		7500651.22.01.00246
-----	---	---------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>