



13	12	11	10	9	8	7	6	5	4	3	2	1
MATERIAL NO.	ENGINEERING NO.	LENGTH	WIRE CUT LENGTH									
849070007	84907-0007	12.00 +1.75-0 (304.8 +44.5-0)	13.25 IN (336.6mm)									

MALE FACE VIEW





1	BROWN
2	WHITE
3	BLUE
4	BLACK

WIRING DIAGRAM



REAR VIEW



REF. PANEL KNOCK-OUT

NOTES:

1. MATERIALS: SEE TABLE
2. FINISHES: SEE TABLE
3. ELECTRICAL SPECIFICATIONS:
VOLTAGE RATING: 250V
CURRENT RATING: 4 AMPS
4. LABEL IS MARKED WITH PART NO., DATE CODE, VOLTAGE AND CURRENT RATING
5. LABEL IS ATTACHED TO BLUE WIRE (CIR. 3)
6. ASSEMBLY IS ROHS COMPLIANT BY EXEMPTION (*).

7	1	LABEL	VINYL	BLACK/YELLOW
6	1	LOCKNUT, PANEL, 1/2 NPT	STEEL	ZINC PLATED
5	1	GASKET	NEOPRENE	BLACK
4	4	CONTACT PIN	BRASS *	TIN PLATED
3	1	INSULATOR, 4/C, DC KEY	NYLON	BLACK
2	1	RECEPTACLE SHELL	STAINLESS STEEL	PASSIVATED
1	4	WIRE, 22 AWG	PVC INSULATION	AS NOTED
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH

RELEASED FOR BUILD
EC NO: WNA2009-0005
DRAWN BY: DRWINSTONE 2008/07/09
CHKD: J. JOZWIK
APPR: J. MURPHY 2008/08/18

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .005	± .0005
2 PLACES	± .005	± .001
1 PLACE	± 0.3	± .012

ANGULAR ± .005°

DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY: R. STONE
DATE: 2008/07/02

CHECKED BY: K. JOZWIK
DATE: 2008/07/07

APPROVED BY: J. MURPHY
DATE: 2008/07/10

MATERIAL NO. SEE CHART

SIZE: C

SCALE: 2:1
DESIGN UNITS: INCH

THIRD ANGLE PROJECTION

TITLE: MIC-C RECEPTACLE, 4/C MALE, DC KEY, 22 AWG 1/2 NPT, SS

MOLEX INCORPORATED

DOCUMENT NO. SD-84907-012

SHEET NO. 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION