


LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
G		14								F		REVISED PER 0720-0121-94		21 JUL 94		OKS DAP	

METRIC

DIMENSIONS LISTED IN mm [INCHES]



AMP WIRE RANGE	UL E13288 Listed
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED
SR LR7189 Certified	MILITARY P/N AND CLASS
12-10 AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP AMP 12-10* APPROX AS SHOWN

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± 0.13 [.005]
3 PLC DEC ± -
ANGLES ± -

DR 6-17-93
TA BRINKMAN
CHK 6-17-93
DA PATTERSON

AMP AMP Incorporated
Harrisburg, PA 17105-3608

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

VOLTAGE RATING:
NOT APPLICABLE

MATERIAL
COPPER PER
ASTM B-152
ANNEALED

APPD 6-17-93
DE MILLER

NAME
TERMINAL, RECTANGULAR
TONGUE, SOLISTRAND™

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

WIRE CROSS SECTIONAL AREA RANGE:
2.62-6.64mm² [5,180-13,100] CIR MILS
SOLID OR STRANDED

FINISH
TIN PLATE
0.00254 [0.00100] MIN
THK PER MIL-T-10727

APPD 6-17-93
JL MECKLEY

PRODUCT SPEC
-

SIZE
C 00779
DRAWING NO
C=55799

FOR ORDER ENTRY
1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

APPLICATION SPEC
-

WEIGHT -

SCALE 4:1
SHEET 1 OF 1