

Aluminum Electrolytic Capacitors Radial Low Leakage Current



013 RLC standard leakage current → 036 RSP

Fig. 1



FEATURES

- Useful life at +85 °C: 3000 h
- Low leakage current, low energy consumption
- Miniaturized, high CV-product per unit volume
- Natural pitch 2.5 mm and 5 mm
- Polarized aluminum electrolytic capacitors, non-solid electrolyte
- Radial leads, cylindrical aluminum case, all-insulated (light blue)
- Charge and discharge proof
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Telecommunication, automotive, audio-video, EDP and industrial
- Coupling, decoupling, buffering, timing, energy storage
- Portable and mobile equipment
- Low surface demand on printed-circuit board

MARKING

The capacitors are marked (where possible) with the following information:

- Rated capacitance (in μ F)
- Tolerance on rated capacitance, code letter in accordance with IEC 60062 (M for $\pm 20\%$)
- Rated voltage (in V)
- Date code in accordance with IEC 60062
- Code indicating factory of origin
- Name of manufacturer
- “-”-sign on top to identify the negative terminal
- Series number (013)

QUICK REFERENCE DATA	
DESCRIPTION	VALUE
Nominal case sizes (\varnothing D x L in mm)	5 x 11 and 8.2 x 11
Rated capacitance range, C_R	2.2 μ F to 470 μ F
Tolerance on C_R	$\pm 20\%$; $\pm 10\%$ on request
Rated voltage range, U_R	6.3 V to 50 V
Category temperature range	-40 °C to +85 °C
Leakage current after 2 min: $U_R = 6.3$ V to 25 V	0.002 C_R x U_R or 0.7 μ A, whichever is greater
$U_R = 35$ V and 50 V	0.002 C_R x U_R + 1 μ A
Endurance test at 85 °C	2000 h
Useful life at 105 °C	750 h
Useful life at 85 °C	3000 h
Useful life at 40 °C, 1.4 x I_R applied	80 000 h
Shelf life at 0 V, 85 °C	500 h
Based on sectional specification	IEC 60384-4 / EN 130300
Climatic category IEC 60068	40 / 085 / 56

C_R (μ F)	SELECTION CHART FOR C_R , U_R , AND RELEVANT NOMINAL CASE SIZES (\varnothing D x L in mm)					
	6.3	10	16	25	35	50
2.2	-	-	-	5 x 11	-	5 x 11
3.3	-	-	-	5 x 11	-	5 x 11
4.7	-	-	-	5 x 11	-	5 x 11
10	-	-	-	5 x 11	-	5 x 11
22	-	-	-	5 x 11	-	5 x 11
33	-	-	5 x 11	-	5 x 11	8.2 x 11
47	-	5 x 11	5 x 11	8.2 x 11	-	8.2 x 11
68	-	5 x 11	-	-	-	8.2 x 11
100	-	5 x 11	-	-	8.2 x 11	-
220	-	8.2 x 11	-	-	-	-
330	8.2 x 11	-	-	-	-	-
470	8.2 x 11	-	-	-	-	-





DIMENSIONS in millimeters **AND AVAILABLE FORMS**

Fig. 2 - Form CA: Long leads

Fig. 3 - Form CB: Cut leads

Case Ø D x L = 5 mm x 11 mm and 8.2 mm x 11 mm
Pitch F = 5 mm

Case Ø D x L = 5 mm x 11 mm only
Pitch F = 2.5 mm

Fig. 4 - Form TFA: Taped in box (ammopack)
Fig. 5 - Form TNA: Taped in box (ammopack)

DIMENSIONS in millimeters, MASS AND PACKAGING QUANTITIES							PACKAGING QUANTITIES	
NOMINAL CASE SIZE Ø D x L	CASE CODE	Ø d	Ø D_{max.}	L_{max.}	F	MASS (g)	FORM CA, CB	
5 x 11	11	0.5	5.5	12	2.5 ± 0.5	≈ 0.4	1000	2000
8.2 x 11	13	0.6	8.7	12	5.0 ± 0.5	≈ 1.1	1000	1000

Note

- For detailed tape dimensions, please see www.vishay.com/doc?28360.

ELECTRICAL DATA	
SYMBOL	DESCRIPTION
C_R	Rated capacitance at 100 Hz, tolerance $\pm 20\%$
I_R	Rated RMS ripple current at 100 Hz, 85 °C
I_{L2}	Max. leakage current after 2 min at U_R
$\tan \delta$	Max. dissipation factor at 100 Hz
Z	Max. impedance at 10 kHz and + 20 °C

Note

- Unless otherwise specified, all electrical values in Table 1 apply at $T_{amb} = 20\text{ }^{\circ}\text{C}$, $P = 86\text{ kPa}$ to 106 kPa , $RH = 45\%$ to 75% .

ORDERING EXAMPLE

Electrolytic capacitor 013 series

 100 μF / 16 V; $\pm 20\%$

Nominal case size: Ø 8.2 mm x 11 mm; Form TFA

Ordering Code: MAL201335101E3

Former 12NC: 2222 013 35101

Table 1

ELECTRICAL DATA AND ORDERING INFORMATION														
U_R (V)	C_R 100 Hz (μF)	NOMINAL CASE SIZE Ø D x L (mm)	I_R 100 Hz 85 °C (mA)	I_{L2} 2 min (μA)	$\tan \delta$ 100 Hz	Z 10 kHz (Ω)	ORDERING CODE MAL2013.....							
							BULK PACKAGING				TAPED AMMOPACK			
							LONG LEADS	CUT LEADS	FORM CA	F (mm)	FORM CB	F (mm)		
6.3	330	8.2 x 11	210	4.2	0.2	0.9	53331E3	5.0	63331E3	5.0	33331E3	5.0	-	-
	470	8.2 x 11	250	5.9	0.2	0.64	53471E3	5.0	63471E3	5.0	33471E3	5.0	-	-
10	47	5 x 11	75	1.0	0.16	2.8	54479E3	2.5	-	-	34479E3	5.0	74479E3	2.5
	68	5 x 11	90	1.4	0.16	2.5	54689E3	2.5	-	-	34689E3	5.0	74689E3	2.5
	100	5 x 11	110	2.0	0.16	1.7	54101E3	2.5	-	-	34101E3	5.0	74101E3	2.5
	220	8.2 x 11	190	4.4	0.16	0.9	54221E3	5.0	64221E3	5.0	34221E3	5.0	-	-
16	33	5 x 11	70	1.1	0.13	2.8	55339E3	2.5	-	-	35339E3	5.0	75339E3	2.5
	47	5 x 11	85	1.5	0.13	2.1	55479E3	2.5	-	-	35479E3	5.0	75479E3	2.5
	100	8.2 x 11	150	3.2	0.13	1.0	55101E3	5.0	65101E3	5.0	35101E3	5.0	-	-
25	2.2	5 x 11	10	0.7	0.06	18	56228E3	2.5	-	-	36228E3	5.0	76228E3	2.5
	3.3	5 x 11	18	0.7	0.06	12	56338E3	2.5	-	-	36338E3	5.0	76338E3	2.5
	4.7	5 x 11	25	0.7	0.06	8.5	56478E3	2.5	-	-	36478E3	5.0	76478E3	2.5
	10	5 x 11	50	0.7	0.06	4.0	56109E3	2.5	-	-	36109E3	5.0	76109E3	2.5
	22	5 x 11	75	1.1	0.08	2.7	56229E3	2.5	-	-	36229E3	5.0	76229E3	2.5
	47	8.2 x 11	130	2.4	0.08	1.3	56479E3	5.0	66479E3	5.0	36479E3	5.0	-	-
35	33	5 x 11	70	3.3	0.13	2.8	50339E3	2.5	-	-	30339E3	5.0	70339E3	2.5
	100	8.2 x 11	150	8.0	0.13	1.0	50101E3	5.0	60101E3	5.0	30101E3	5.0	-	-
50	2.2	5 x 11	20	1.2	0.06	18	51228E3	2.5	-	-	31228E3	5.0	71228E3	2.5
	3.3	5 x 11	32	1.3	0.06	12	51338E3	2.5	-	-	31338E3	5.0	71338E3	2.5
	4.7	5 x 11	38	1.5	0.06	8.5	51478E3	2.5	-	-	31478E3	5.0	71478E3	2.5
	10	5 x 11	55	2.0	0.06	4.0	51109E3	2.5	-	-	31109E3	5.0	71109E3	2.5
	22	5 x 11	75	3.2	0.08	2.7	51229E3	2.5	-	-	31229E3	5.0	71229E3	2.5
	33	8.2 x 11	110	4.3	0.06	1.4	51339E3	5.0	61339E3	5.0	31339E3	5.0	-	-
	47	8.2 x 11	130	5.7	0.08	1.3	51479E3	5.0	61479E3	5.0	31479E3	5.0	-	-
	68	8.2 x 11	150	7.8	0.08	1.2	51689E3	5.0	61689E3	5.0	31689E3	5.0	-	-

ADDITIONAL ELECTRICAL DATA

PARAMETER	CONDITIONS	VALUE
Voltage		
Surge voltage		$U_S \leq 1.3 \times U_R$
Reverse voltage		$U_{rev} \leq 1 \text{ V}$
Current		
Leakage current	After 2 min at U_R : $U_R = 6.3 \text{ V to } 25 \text{ V}$ $U_R = 35 \text{ V and } 50 \text{ V}$	$I_{L2} \leq 0.002 C_R \times U_R$ or $0.7 \mu\text{A}$, whichever is greater $I_{L2} \leq 0.002 C_R \times U_R + 1 \mu\text{A}$
Inductance		
Equivalent series inductance (ESL)	Case $\emptyset D \times L = 5 \text{ mm} \times 11 \text{ mm}$	Typ. 13 nH
	Case $\emptyset D \times L = 8.2 \text{ mm} \times 11 \text{ mm}$	Typ. 16 nH
Resistance		
Equivalent series resistance (ESR)	Calculated from $\tan \delta_{max}$ and C_R (see Table 1)	$ESR = \tan \delta/2 \pi f C_R$


CAPACITANCE (C)


Fig. 6 - Typical multiplier of capacitance as a function of ambient temperature




Fig. 7 - Typical multiplier of capacitance as a function of frequency


LEAKAGE CURRENT


Fig. 8 - Typical multiplier of leakage current as a function of ambient temperature




Fig. 9 - Typical multiplier of leakage current as a function of time


LEAKAGE CURRENT


Fig. 10 - Typical multiplier of leakage current as a function of time


RIPPLE CURRENT AND USEFUL LIFE


Fig. 11 - Multiplier of useful life as a function of ambient temperature and ripple current load

Table 2

MULTIPLIER OF RIPPLE CURRENT (I_R) AS A FUNCTION OF FREQUENCY			
FREQUENCY (Hz)	I _R MULTIPLIER		
	$U_R = 6.3$ V	$U_R = 10$ V, 16 V, and 35 V	$U_R = 25$ V and 50 V
50	0.90	0.85	0.80
100	1.00	1.00	1.00
300	1.12	1.20	1.25
1000	1.20	1.30	1.40
3000	1.25	1.35	1.50
$\geq 10\,000$	1.30	1.40	1.60

Table 3

TEST PROCEDURES AND REQUIREMENTS			
TEST		PROCEDURE	REQUIREMENTS
NAME OF TEST	REFERENCE		
Endurance	IEC 60384-4 / EN130300, subclause 4.13	$T_{amb} = 85^{\circ}C$; U_R applied; 2000 h	$U_R \leq 6.3 \text{ V}$; $\Delta C/C: +15\% / -30\%$ $U_R > 6.3 \text{ V}$; $\Delta C/C: \pm 15\%$ $\tan \delta \leq 1.3 \times \text{spec. limit}$ $Z \leq 2 \times \text{spec. limit}$ $I_{L2} \leq \text{spec. limit}$
Useful life	CECC 30301, subclause 1.8.1	$T_{amb} = 85^{\circ}C$; U_R and I_R applied; 3000 h	$U_R \leq 6.3 \text{ V}$; $\Delta C/C: +45\% / -50\%$ $U_R > 6.3 \text{ V}$; $\Delta C/C: \pm 45\%$ $\tan \delta \leq 3 \times \text{spec. limit}$ $Z \leq 3 \times \text{spec. limit}$ $I_{L2} \leq \text{spec. limit}$ no short or open circuit total failure percentage: $\leq 1\%$
Shelf life (storage at high temperature)	IEC 60384-4 / EN130300, subclause 4.17	$T_{amb} = 85^{\circ}C$; no voltage applied; 500 h After test: U_R to be applied for 30 min, 24 h to 48 h before measurement	$\Delta C/C, \tan \delta, Z$: For requirements see "Endurance test" above $I_{L2} \leq 2 \times \text{spec. limit}$

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.