




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

1. TUSONIX STANDARD PART NUMBER: 4261-001.
TUSONIX RoHS COMPLIANT PART NUMBER: 4261-001 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
3. PART MARKING: TUSONIX TRADEMARK AND VARIATION.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

5,500	50 VDC	3 A	10 G Ω	125 VDC	7	14	30	55	70	70
MIN. CAP.(pf)	+125 °C DC WORKING VOLTAGE	CURRENT	IR (MIN.) @ 100 VDC	DWV	3 MHz	10 MHz	30 MHz	100 MHz	300 MHz	1 GHz
MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220										
X-2015 Rev-0 REVISION RECORD	0	1	2	3	--TOLERANCES-- Unless Otherwise Specified DECIMAL ± .031 [0.79] ANGLES ±					
	Original Release C.O. 6611	RDN TO COMP FMT. S.M. 06-19-02	ADDED NOTES 1-3. S.M. 04-27-05	20050420-2-02						
	DIM'S REV. TITLE CHGD. E.C. 5-26-92	6667	20020604-3-02	20050420-2-02						
					TUSONIX TUCSON, ARIZONA					
					Title MULTI LAYER BUSHING STYLE EMI FILTER Drawn S. M. 06-19-02 Scale 4 X Approved J.Mc. 06-19-02 A 4261-001					