





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
V		REVISED PER ECO-15-015252	13NOV15	BJ	FY



SECTION T-T

RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.K. SEIFRIED 05/14/90	TE Connectivity	
		CHK G.SKIPPER 01/22/92		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD G.SKIPPER 01/22/92	NAME	ASSY, HDI, 4 ROW, RIGHT ANGLE PIN 3.05 [.120] LONG SOLDER TAILS
	0 PLC ± -	PRODUCT SPEC	SIZE	CAGE CODE DRAWING NO
	1 PLC ± -	APPLICATION SPEC	WEIGHT	RESTRICTED TO
MATERIAL	FINISH	SCALE	100779	533286
CUSTOMER DRAWING		4:1	SHEET 1 OF 2	REV V

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT 2005 By - ALL RIGHTS RESERVED,		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

1 HOUSING MATERIAL: THERMOPLASTIC, COLOR-BLACK.

2 CONTACT MATERIAL: PHOSPHOR BRONZE.

3 FINISH:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-9063; BASED ON TELCORDIA DR-1217-CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
SOLDER TAILS AREA: TIN-LEAD PLATED.

4 RIGHT ANGLE PIN RECOMMENDED P.C. BOARD HOLE SIZES ARE
0.94-1.09 [.037-.043]; RECOMMENDED PAD DIA IS 1.52 [.060].

5 MOUNTING EARS AND HARDWARE PURCHASED SEPARATELY, KIT PART NUMBER 533050-1.

6. DIMENSIONS IN BRACKETS ARE IN INCHES.

 HOUSINGS WITH CENTER MOUNTING IS RECOMMENDED FOR ASSEMBLIES HAVING 75 CONTACTS PER ROW OR MORE.



△ 8 PART NUMBER IS OBSOLETE.

9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

A	144.78 [5.700]	-57-	148.59 [5.850]	158.75 [6.250]	166.37 [6.550]	-232	3-533286-5
B	134.62 [5.300]	-53-	138.43 [5.450]	148.59 [5.850]	156.21 [6.150]	-216	3-533286-4
	-	-	-	-	-	-	3-533286-3
	-	-	-	-	-	-	3-533286-2
	-	-	-	-	-	-	3-533286-1
	-	-	-	-	-	-	3-533286-0
	-	-	-	-	-	-	2-533286-9
	-	-	-	-	-	-	2-533286-8
	-	-	-	-	-	-	2-533286-7
	-	-	-	-	-	-	2-533286-6
	-	-	-	-	-	-	2-533286-5
	-	-	-	-	-	-	2-533286-4
	-	-	-	-	-	-	2-533286-3
	-	-	-	-	-	-	2-533286-2
	-	-	-	-	-	-	2-533286-1
	-	-	-	-	-	-	2-533286-0
	-	-	-	-	-	-	1-533286-9
-	-	-	-	-	-	1-533286-8	
E	-	-	-	-	-	-	1-533286-7
	-	-	-	-	-	-	1-533286-6
A	93.98 [3.700]	-37-	97.79 [3.850]	107.95 [4.250]	115.57 [4.550]	-152	1-533286-5
B	210.82 [8.300]	-83-	214.63 [8.450]	224.79 [8.850]	232.41 [9.150]	-336	1-533286-4
A	200.66 [7.900]	-79-	204.47 [8.050]	214.63 [8.450]	222.25 [8.750]	-320	1-533286-3
E	187.96 [7.400]	74	191.77 [7.550]	201.93 [7.950]	209.55 [8.250]	300	1-533286-2
A	175.26 [6.900]	-69-	179.07 [7.050]	189.23 [7.450]	196.85 [7.750]	-280	1-533286-1
B	162.56 [6.400]	-64-	166.37 [6.550]	176.53 [6.950]	184.15 [7.250]	-260	1-533286-0
	149.86 [5.900]	59	153.67 [6.050]	163.83 [6.450]	171.45 [6.750]	240	533286-9
	137.16 [5.400]	-54-	140.97 [5.550]	151.13 [5.950]	158.75 [6.250]	-220	533286-8
A	124.46 [4.900]	-49-	128.27 [5.050]	138.43 [5.450]	146.05 [5.750]	-200	533286-7
	111.76 [4.400]	44	115.57 [4.550]	125.73 [4.950]	133.35 [5.250]	180	533286-6
	99.06 [3.900]	39	102.87 [4.050]	113.03 [4.450]	120.65 [4.750]	160	533286-5
	86.36 [3.400]	-34-	90.17 [3.550]	100.33 [3.950]	107.95 [4.250]	-140	533286-4
	78.74 [3.100]	31	82.55 [3.250]	92.71 [3.650]	100.33 [3.950]	128	533286-3
	73.66 [2.900]	29	77.47 [3.050]	87.63 [3.450]	95.25 [3.750]	120	533286-2
	60.96 [2.400]	24	64.77 [2.550]	74.93 [2.950]	82.55 [3.250]	100	533286-1
	E	D	C	B	A	POSN	PART NUMBER

OBSOLETE

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWG R.K. SEIFRED	05/14/90			TE Connectivity	
				CHK. G.SKIPPER	01/22/92				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		RWD G.SKIPPER	01/22/92	NAME	ASSY.HD1,4 RPO,RIGHT ANGLE PIN 3.05 [.120] LONG SOLDER TAILS		
		1 P/LC ± — 2 P/LC ± — 3 P/LC ± — 4 P/LC ± 0.13 [.005] ANGLES ± —		PRODUCT SPEC —					
MATERIAL		FINISH		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				WEIGHT 0		A1	00779	 533286	—
CUSTOMER DRAWING						SCALE		4:1	SHEET
								2	2
								REV	V