






1. INTERPRET DRAWING PER ASME Y14.5M-1994
2. VARIATION IN PLATING COLOR IS NORMAL AND ALLOWED.
3. MAXIMUM PIN LEAN OF 8° IN ANY DIRECTION.
4. 0,2mm MAXIMUM BURR ALLOWED.
5. RoHS COMPLIANT AND CERTIFIED.

REVISION	INFO	REV.
RELEASE	OS60-0321-04	○
	DA 12-22-04	
	APP'D: BP 12-22-04	
REVISED	OS60-0103-05	A
	ITAO 6-7-05	
	APP'D: B.P. 6-16-05	
RELEASED	CCO-08-007831	A1
	ITAO 3-30-08	
	APP'D: B.P. 4-2-08	

DO NOT SCALE	 Tyco Electronics		Norwood, Massachusetts 02062		
	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE: X, X ± .5 X, XX ± .25 X, XXX ± .0 ANGLES ± °	DRAWN BY: D. AMARAL	DATE: 12-22-04	MATERIAL: 6063-T5 CAST ALUMINUM	
		ENGINEER: B. PETROCELLI	DATE: 12-22-04	FINISH: IMERSION NICKEL PLATED	
		FILENAME	PROJECT		SYSTEM
		PRO-E			

CONFIDENTIAL. PROPERTY OF TYCO ELECTRONICS. NOT TO BE DISCLOSED TO OTHERS, REPRODUCED OR USED FOR ANY PURPOSES EXCEPT AS AUTHORIZED IN WRITING BY AN AUTHORIZED OFFICER OF TYCO ELECTRONICS. MUST BE RETURNED TO TYCO ELECTRONICS ON DEMAND, ON COMPLETION OF ORDERS OR OTHER PURPOSES FOR WHICH LOANED.		TITLE: HEATSINK SFP 4,2MM TALL	
DIMENSIONS ARE IN: MILLIMETERS	SCALE: 4:1	TE PART NO.: 1542992-2	SHEET 1 of 1
THIRD ANGLE PROJECTION	SIZE C	DWG. NO.: C-1542992	REV. A