


(2.54 mm) .100"



THROUGH-HOLE .025" SQ POST SOCKET

SPECIFICATIONS

For complete specifications see www.samtec.com?SSW or www.samtec.com?SSQ

Insulator Material:

Black Liquid Crystal Polymer (-S & -D) or Black High Temperature Thermoplastic (-T)

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over 50 μ " (1.27 μ m) Ni

Current Rating (SSW/TSM):

4.7 A per pin (1 pin powered per row)

Current Rating (SSQ/TSW):

6.3 A per pin (1 pin powered per row)

Operating Temp Range:

-55 °C to +125 °C with Gold
-55 °C to +105 °C with Tin

Insertion Depth:

(3.68 mm) .145" to (6.35 mm) .250"

Normal Force:

Standard= 125 grams (4.4 N)

Max Cycles:

100 with 10 μ " (0.25 μ m) Au

Voltage Rating:

465 VAC / 655 VDC

RoHS Compliant:

Yes

Mates With:

TSW, MTSW, MTLW,
EW, ZW, TSS, ZSS,
TSM, TSSH, HTSS




TYPE STRIP

SSW = Solder Tail

SSQ = Square Tail

PIN CENTERS

-1 = (2.54 mm) .100" Centers



NO. PINS PER ROW

PROCESSING

Lead-Free Solderable:

Yes:

-S and -D row option

Wave only:


-P, -T and -Q row option

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




Note:
Some lengths, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.



SSW, SSQ SERIES

LEAD STYLE

PLATING OPTION

ROW OPTION

TAIL OPTION

OTHER OPTION

-F

= Gold flash on contact,
Matte Tin on tail

-L

= 10 μ " (0.25 μ m) Gold on contact,
Matte Tin on tail

-G

= 20 μ " (0.51 μ m) Gold on contact,
Gold flash on tail

-T

= Matte Tin
(-T N/A on LIF contacts)

-S

= Single Row

-P

= Single Row
(36 pins max)

-D

= Double Row

-T

= Triple Row

-Q

= Double Row
.200" (5.08 mm) row space
(Outer rows filled only)

-RA

= Right-angle
(Leave blank for
straight pin
version)

-LL

= Locking Lead

Two leads per strip crimped in opposite
directions on or near centerline.
Available on tails from (2.29 mm) .090"
to (7.87 mm) .310" only. N/A with single
row 1 or 2 positions.

-“XXX”

= Polarized
(Specify “XXX” as position number)

ALSO AVAILABLE (MOQ Required)


- Other platings
 - Notch option
- Contact Samtec.

Straight Pin Versions (Specify “LEAD STYLE” from chart)

LEAD STYLE		SINGLE DOUBLE OR TRIPLE A
Standard Insertion Force	Low Insertion Force*	
-01	-21	(2.64) .104
-02	-22	(4.93) .194
-03	-23	(10.00) .394
-04	-24	(14.83) .584
-06**	N/A	(3.15) .124

* LIF N/A with Tin Plating


**Style -06 N/A with SSQ



Right-angle Versions (Specify “LEAD STYLE” from chart)

LEAD STYLE		SINGLE (-S & -P) A	DOUBLE (-D) A	TRIPLE (-T & -Q) A
Standard Insertion Force	Low Insertion Force*			
-02	-22	(2.54) .100	(2.54) .100	(2.54) .100
-03	-23	(7.62) .300	(7.62) .300	N/A
-04	-24	(12.45) .490	N/A	N/A

*LIF N/A with Tin Plating



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.