



## ◎ 高度不含離形紙厚度

QMFZ2 Component - Plastics

Wednesday, September 15, 2004

E41938

E I DUPONT DE NEMOURS & CO INC

ENGINEERING POLYMERS CHESTNUT RUN PLAZA PO BOX 80713 WILMINGTON DE 19880

Material Designation: 101(+)(f1), 101F(+)(f1), 101L(+)(f1), E101(+)(f1), E101L(f1), 132F(+)(f1), 135F(+)(f1)

Product Description: Polyamide 66 (PA66), designated "Zytel" furnished as pellets.

Color	Min. Thick. (mm)	Flame Class	HWI	HAI	RTI Elec	RTI Imp	RTI Str	IEC GWIT	IEC GWFI
ALL	0.71	V-2	4	0	130	75	85	725	960
	1.5	V-2	3	0	130	75	85	750	960
	3.0	V-2	2	0	130	75	85	800	960
	6.0	V-2	2	0	130	75	85	800	960

CTI: 0 IEC CTI: -

HVTR: 0 D495: 6

IEC Ball Pressure (°C): -

Dielectric Strength (kV/mm): 13

Volume Resistivity (10<sup>12</sup>ohm-cm): 14

Dimensional Stability(%): -

ISO Tensile Strength (MPa): -

ISO Flexural Strength (MPa): -

ISO Heat Deflection (°C): -

ISO Tensile Impact (kJ/m<sup>2</sup>): -

ISO Izod Impact (kJ/m<sup>2</sup>): -

ISO Charpy Impact (kJ/m<sup>2</sup>): -



核發章

◎ ROHS compliant

DRAW NO. PGAS007387 C GJS

TOLERANCE: L≤10 ±0.2 10<L≤30 ±0.3 30<L≤50 ±0.5 50<L≤100 ±0.7 100<L≤250 ±1.2 ABOVE 250 ±1.5	APPROVED BY	張道陽	2007.05.30.	 品固企業股份有限公司 品基電子(東莞)有限公司 蘇州品基電子科技有限公司 鑽隆有限公司 PINGOOD ENTERPRISE CO.,LTD.
	REVIEWED BY	謝怡嘉	2007.05.30.	
	DRAWN BY	張博欽	2007.05.30.	
	MATERIAL: NYLON 66(UL)			
FLAME CLASS: 94V-2		PART NAME:	電線固定座	REV.
COLOR: NATURAL		WIRE MOUNT	A	4
ADHESIVE TAPE: 3M(4032)/3M(1600T) or EQUIVALENT		PART NO:	FW-1S-3M	SIZE
				SHEET 1 OF 1

EF0404505