


REVISED FOR PUBLICATION		REVISIONS	
DATE	DESCRIPTION	DATE	BY
GP 00		17/08/03	BM WM
H	REVISED FOR ESD-00-007327		



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
- 2.
3. COVER SHOWN LOOSE BUT SHIPPED ASSEMBLED.
4. WIRE RANGE: 26 AWG. SOLID THRU 30 AWG SOLID AND 28 AWG. STRANDED RIBBON CABLE.
5. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
6. FLAT CABLE SHALL BE FURNISHED BY CUSTOMER.
7. MATING FACE CONSISTS OF TWO ROWS OF TERMINALS ON .085 CENTERS. TERMINATING SIDE CONSISTS OF TERMINALS ON .100 CENTERS FOR AN EFFECTIVE .050 TERMINATION.
8. FOR MORE INFORMATION REFER TO AMP PRODUCT SPECIFICATION 108-6076 & APPLICATION SPEC 114-6030.

THIS DRAWING IS A CONTROLLED DOCUMENT		DATE 15/04/07		BY 1000 Electronics Corporation	
DIMENSIONS IN INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED		DATE 15/04/07	
0.0005	0.0005	0.0005	0.0005	1000 Electronics Corporation	
0.0005	0.0005	0.0005	0.0005	Harrisburg, PA 17105-3008	
0.0005	0.0005	0.0005	0.0005	RECEPTACLE ASSEMBLY, 14 POSITION	
0.0005	0.0005	0.0005	0.0005	SCREW CHAMP LATCH	
0.0005	0.0005	0.0005	0.0005	APPLICATION SPEC	
0.0005	0.0005	0.0005	0.0005	SIZE 0.0005 (DRAWING NO)	
0.0005	0.0005	0.0005	0.0005	A2100779	
0.0005	0.0005	0.0005	0.0005	5535397	
0.0005	0.0005	0.0005	0.0005	SCALE 2:1	
0.0005	0.0005	0.0005	0.0005	SHEET 1 OF 1	
0.0005	0.0005	0.0005	0.0005	REV H	