

LOC		DIST		REVISONS				
AD	25	IF	LTR	DESCRIPTION		DATE	DWN	APVD
		01		REVISED PER ECO-08-013371		05JUN08	DH	DB

- 1

HOUSING MATERIAL: GLASS-FILLED POLYMER.
- 2

CONTACT MATERIAL: COPPER ALLOY.
- 3






PART NUMBER, DATE CODE IDENTIFICATION, CSA LOGO IN THIS APPROXIMATE AREA.
- 4

ACTION PIN POSTS REQUIRE 1.57[.062] MINIMUM THICK PC BOARD. RECOMMENDED PC BOARD DRILLED HOLES ARE $\varnothing 1.151 \pm 0.025 [.0453 \pm .0010]$ WITH 0.02-0.08[.001-.003] COPPER AND 0.008[.0003] MINIMUM TIN-LEAD PLATING. FINISHED HOLES AFTER PLATING $\varnothing 0.94-1.09 [.037-.043]$.
- 5

CONTACT FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN PLATE ON POSTS.
- 6

CONTACT POINT.
- 7

MARKING ON THIS SIDE.



PC BOARD LAYOUT

5148417-5
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE 13APROS	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK A. SHARPE 13APROS	NAME ASSEMBLY, RECEPTACLE, TYPE M, EUROCARD, 78+2, PRESS-FIT, 4.83[.190]	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. SHARPE 13APROS	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		SIZE
1 PLC ± -		—		CAGE CODE
2 PLC ± 0.15[.005]		—		DRAWING NO
3 PLC ± -		—		RESTRICTED TO
4 PLC ± -		—		—
ANGLES ± -		—		—
FINISH		—		—
MATERIAL		—		—
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1