




NOTES:

1. ALL DIMENSIONS IN MM[INCH]

2. GENERAL TOLERANCE: $x.x = \pm 0.4$ $x.xx = \pm 0.25$

3. TERM. NOS. FOR REFERENCE ONLY.

4. RATING: 1A @125VAC, 0.5A @250VAC

5. CONTACT RESISTANCE: 20milli-OHMS MAX.

6. DIELECTRIC STRENGTH: 1,500 V rms @SEA LEVEL

▲7. MATERIALS:

HOUSING: ZINC ALLOY W/CHROME PLATING

CYLINDER: ZINC ALLOY W/CHROME PLATING

TERMINAL AND CONTACTS: SILVER PLATED

KEYS (2) KEY CODE 1001: ZINC ALLOY, CHROME PLATING

8. ▲ DENOTES CRITICAL PARAMETER.

9. 2002/95/EC (ROHS) COMPLIANT

CIRCUIT: SPDT
CONTACT CONFIGURATION
90° INDEXING

SWITCH FUNCTION	
POS 1	POS 2
↑	→
1-2	3-4

LEGEND

= INDICATES KEY PULL POSSIBLE

RECOMENDED PANEL CUTOUT

B	20918	1001 KEY CODE	12/11/12	EBP
A	18810	Release For Production	3/18/10	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE KO105B1001

SCALE	DATE 3/18/2010	DR BLR	DWG K100304	REV B
-------	-------------------	-----------	----------------	----------