





(2,00 mm) .0787"

TLSD SERIES

TLSD-08-D-02.00-01-L-SR



TLSD-12-D-02.00-01-L-RN1



COST EFFECTIVE IDC SOCKET CABLES

Mates with:

TMM, TMMH (Except -SR),
TW, MTMM, TLMM

FEATURES

- Low cost alternative to TCSD
- 1 point of contact phosphor bronze
- Strain Relief for Rugged Applications

SPECIFICATIONS

For complete specifications
see www.samtec.com?TLSD

Insulator Material:

Black Glass Filled Polyester

Contact:

Phosphor Bronze

Plating:

Au or Sn over
50µ" (1,27 µm) Ni

Wire:

28 AWG 7/36 Stranded,
Tinned, Copper with

Gray PVC Insulator

Current Rating:

1A per contact

Operating Temp Range:

-40°C to +105°C

Lead Size Accepted:

(0,48 mm) .019" to

(0,53 mm) .021"

Contact Resistance:

15 mΩ maximum

delta from initial

Insertion Depth:

(3,56 mm) .140" to

(4,27 mm) .168"

Insertion Force:

(Single contact only)

2 oz. (0,56 N) average

Withdrawal Force:

(Single contact only)

1.4 oz (0,39 N) average

RoHS Compliant:

Yes



TYPE	NO. PINS PER ROW	END OPTION	LENGTH	01	PLATING OPTION	OTHER OPTION
	-05, -08, -10, -12, -13, -15, -17, -20, -22, -25 (Call for other sizes)		- "XX.XX" = Assembled Length Assembled Length in INCHES (±1/8") 2 inches minimum		-L = 10µ" (0,25 µm) Gold on contact area	
		-S = Single End				
		-D = Double End				
				-N = Notch Polarization		
						-RW = Reverse Wiring Black wire opposite position #1.
						-RN1 = Reverse Notch End 1 Reverse notch option on end 1 only. Not Available with -R option.
						-RN2 = Reverse Notch End 2 Reverse notch option on end 2 only. Not Available with -R option.
				-SR = Strain Relief		
						-P "XX" = Position Polarization Specify "XX" as position number. Same position will be polarized on both ends.
						-B "XX" = Breakout Specify "XX" as number of conductors to be broken out. Breakout starts with Number 1 lead indicated by brown wire or red stripe. Shown on top side.
						-D "XX" = Daisy Chain Specify "XX" as number of conductors to be broken out. Breakout starts with Number 1 lead indicated by brown wire or red stripe. Shown on top side.
						-R = Reversed
						-M = Middle Reverse Requires -DXX
						-O = Outside Reverse Requires -DXX

POLARIZING KEY

Specify PK-01-07
for polarizing key.
Also polarizes SMM
Series socket strips.

ALSO AVAILABLE

Connector only
(KTLSD Series).
Call Samtec.**Note:** TLSD Series
assemblies are non-
standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
 SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
 SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
 SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683