

Fuses for Semiconductor Protection

Cylindrical Fuses



SIBA cylindrical ultra-rapid fuses are available in six different sizes. They can be fitted with or without a built-in striker pin for fuse blown indication or operation of microswitches.

Approval: 
Standards: IEC 60269-1 and -4
DIN VDE 0636-40
UL 248-13
Classes: gR/aR/gRL (gS)
Current ratings: 100 mA – 250 A

Sizes and voltage ratings:

5 x 20 mm:	AC 250 V
6.35 x 32 mm:	AC 500 – 1000 V
10 x 38 mm:	AC 600 – 1000 V
14 x 51 mm:	AC 500/600V – 690/700 V
22 x 58 mm:	AC 500/600 V – 690/700 V
27 x 60 mm:	AC 660 V – 1000 V

Features / Benefits

- ▶ High interrupting rating up to 300 kA
- ▶ Voltage rating AC 250 V to AC 1000 V
- ▶ Protection of Power Semiconductors according to IEC 60269-1 and -4
- ▶ Available with integrated striker pin
- ▶ Classes according to IEC 60269-4 and DIN VDE 0636-40
- ▶ Fuse-holder / fuse-clips and accessories are available



Fuses for Semiconductor Protection

Cylindrical Fuses

Selection Guide Fuse-Links

Size	Rated Voltage	Indicator Type	Part No.	Selector Guide [Page]	Techn. Data [Page]	
5 x 20	AC 250 V	–	70 001 40	URZ 4	URZ 16	
5 x 20	AC 250 V	–	70 007 40	URZ 4	URZ 16	
6.35 x 32	AC 500/700 V	–	70 125 40	URZ 5	URZ 18	
6.35 x 32	AC 400 V	–	70 065 84	URZ 5	URZ 17	
6.35 x 32	AC/DC 1000 V	–	70 172 40	URZ 6	URZ 19	
10 x 38	AC 600 V	–	60 034 34	URZ 7	URZ 20	
10 x 38	AC 600 V	–	60 064 34	URZ 7	URZ 20	
10 x 38	AC 600 V	–	60 033 05	URZ 7	URZ 21	
10 x 38	AC 660 V	–	50 179 06	URZ 8	URZ 22	
10 x 38	AC/DC 1000 V	–	50 199 06	URZ 8	URZ 23	
10 x 35	AC/DC 1000 V	–	50 210 06	URZ 8	URZ 24	
14 x 51	AC 500/600 V	–	50 058 06	URZ 9	URZ 25	
14 x 51	AC 500/600 V	with striker	50 059 06	URZ 9	URZ 25	
14 x 51	AC 690 V	–	50 124 06	URZ 9	URZ 27	
14 x 51	AC 690 V	with striker	50 126 06	URZ 9	URZ 27	
14 x 51	AC 690 V	–	50 124 34	URZ 10	URZ 26	
14 x 51	AC 690 V	with striker	50 126 34	URZ 10	URZ 26	
14 x 51	DC 700 V	–	50 118 06	URZ 11	URZ 28	
14 x 51	DC 700 V	–	50 201 06	URZ 11	URZ 29	
22 x 58	AC 500/660 V	–	50 060 06	URZ 12	URZ 30	
22 x 58	AC 500/660 V	with striker	50 061 06	URZ 12	URZ 30	
22 x 58	AC 690 V	–	50 140 06	URZ 12	URZ 31	
22 x 58	AC 690 V	with striker	50 142 06	URZ 12	URZ 31	
22 x 58	AC 690 V	–	50 140 34	URZ 13	URZ 32	
22 x 58	AC 690 V	with striker	50 142 34	URZ 13	URZ 32	
27 x 60	AC 660 V	–	50 193 20	URZ 14	URZ 33	
27 x 60	AC 660 V	with striker	50 194 20	URZ 14	URZ 33	
27 x 60	AC 1000 V	–	50 196 20	URZ 14	URZ 34	
27 x 60	AC 1000 V	with striker	50 197 20	URZ 14	URZ 34	
27 x 60	DC 660 V	–	50 190 06	URZ 15	URZ 35	



Fuses for Semiconductor Protection

Cylindrical Fuses

Selection Guide Fuse-Holder ZS-Modul

ZS-Module	Number of Poles	Indicator Type	Part No.	Techn. Data [Page]	
10 x 38	1	-	51 063 04.DC	URZ 37	
10 x 38	1	-	51 063 04	URZ 37	
10 x 38	2	-	51 063 04.2	URZ 37	
10 x 38	3	-	51 063 04.3	URZ 37	
10 x 38	1	LED indicator	51 063 04.L	URZ 37	
10 x 38	2	LED indicator	51 063 04.2L	URZ 37	
10 x 38	3	LED indicator	51 063 04.3L	URZ 37	
14 x 51	1	-	51 058 04	URZ 37	
14 x 51	2	-	51 058 04.2	URZ 37	
14 x 51	3	-	51 058 04.3	URZ 37	
14 x 51	1	micro switch	51 058 04.S	URZ 37	
14 x 51	2	micro switch	51 058 04.2S	URZ 37	
14 x 51	3	micro switch	51 058 04.3S	URZ 37	
22 x 58	1	-	51 060 04	URZ 37	
22 x 58	2	-	51 060 04.2	URZ 37	
22 x 58	3	-	51 060 04.3	URZ 37	
22 x 58	1	micro switch	51 060 04.S	URZ 37	
22 x 58	3	micro switch	51 060 04.3S	URZ 37	

Selection Guide Fuse-Clips

Size	Part No.	Techn. Data [Page]	Type	
10 mm	61 017 01.2	URZ 35		
14 mm	61 001 01.2	URZ 35	screw	
22 mm	61 002 01.3	URZ 35	mountable	
27 mm	61 004 01.3	URZ 35		
14 mm	58 058 06	URZ 36	PCB	
22 mm	58 060 06	URZ 36	mountable	



Fuses for Semiconductor Protection

Cylindrical Fuses


Size
5 x 20 mm

Rated Voltage
AC 250 V

Class
aR

Rated Current [A]	Part No.	Rated Breaking Capacity [kA]	UL Rec.	Weight [kg/100]	Pack	
100 mA	70 001 40.0.100	300	✓	0.14	100	
125 mA	70 001 40.0.125	300	✓	0.14	100	
160 mA	70 001 40.0.160	300	✓	0.14	100	
200 mA	70 001 40.0.200	300	✓	0.14	100	
250 mA	70 001 40.0.250	300	✓	0.14	100	
315 mA	70 001 40.0.315	300	✓	0.14	100	
400 mA	70 001 40.0.400	300	✓	0.14	100	
500 mA	70 001 40.0.500	300	✓	0.14	100	
630 mA	70 001 40.0.630	300	✓	0.14	100	
800 mA	70 001 40.0.800	300	✓	0.14	100	
1	70 001 40.1	300	✓	0.14	100	
1.25	70 001 40.1.25	300	✓	0.14	100	
1.6	70 001 40.1.6	300	✓	0.14	100	
2	70 001 40.2	300	✓	0.14	100	
2.5	70 001 40.2.5	300	✓	0.14	100	
3.15	70 001 40.3.15	300	✓	0.14	100	
4	70 001 40.4	300	✓	0.14	100	
5	70 001 40.5	300	✓	0.14	100	
6.3	70 001 40.6.3	1 500 A		0.14	100	
8	70 001 40.8	1 500 A		0.14	100	
10	70 001 40.10	1 500 A		0.14	100	
6.3	70 007 40.6.3	300	✓	0.14	100	
8	70 007 40.8	300	✓	0.14	100	
10	70 007 40.10	300	✓	0.14	100	
12.5	70 007 40.12.5	300	✓	0.14	100	

A 0.79" (20 mm)
B 0.2" (5 mm)





Fuses for Semiconductor Protection

Cylindrical Fuses

Size
6.35 x 32 mm

Rated Voltage
AC 400 V

Class
gRL(gS)

Rated Current [A]	Part No.	Rated Breaking Capacity [kA]	Rated Voltage [AC]	UL Rec.	Weight [kg/100]	Pack	
6.3	70 065 84.6.3	120 kA	400 V	✓	0.9	10	
8	70 065 84.8	120 kA	400 V	✓	0.9	10	
10	70 065 84.10	120 kA	400 V	✓	0.9	10	
12.5	70 065 84.12.5	120 kA	400 V	✓	0.9	10	
16	70 065 84.16	120 kA	400 V	✓	0.9	10	
20	70 065 84.20	120 kA	400 V	✓	0.9	10	


Size
6.35 x 32 mm

Rated Voltage
AC 500/700 V

Class
aR

Rated Current [A]	Part No.	Rated Breaking Capacity [kA]	Rated Voltage [V]	UL Rec.	c UL	Weight [kg/100]	Pack	
160 mA	70 125 40.0.160	50	700	✓	✓	0.24	100	
200 mA	70 125 40.0.200	50	700	✓	✓	0.24	100	
250 mA	70 125 40.0.250	50	700	✓	✓	0.24	100	
315 mA	70 125 40.0.315	50	700	✓	✓	0.24	100	
400 mA	70 125 40.0.400	50	700	✓	✓	0.24	100	
500 mA	70 125 40.0.500	50	700	✓	✓	0.24	100	
630 mA	70 125 40.0.630	50	700	✓	✓	0.24	100	
800 mA	70 125 40.0.800	50	700	✓	✓	0.24	100	
1	70 125 40.1	50	700	✓	✓	0.24	100	
1.25	70 125 40.1.25	50	700	✓	✓	0.24	100	
1.6	70 125 40.1.6	50	700	✓	✓	0.24	100	
2	70 125 40.2	50	700	✓	✓	0.24	100	
2.5	70 125 40.2.5	50	500	✓	✓	0.24	100	
3.15	70 125 40.3.15	50	500	✓	✓	0.24	100	
4	70 125 40.4	50	500	✓	✓	0.24	100	
5	70 125 40.5	50	500	✓	✓	0.24	100	
6.3	70 125 40.6.3	50	500	✓	✓	0.24	100	
8 ¹	70 125 40.8	50	500	✓	✓	0.24	100	
10 ¹	70 125 40.10	50	500	✓	✓	0.24	100	
12.5 ¹	70 125 40.12.5	50	500	✓	✓	0.24	100	
16 ¹	70 125 40.16	50	500	✓	✓	0.24	100	
20 ¹	70 125 40.20	50	500	✓	✓	0.24	100	

¹ Consideration should be given to heat dissipation.



A 1.26" (32 mm)
B 0.25" (6.35 mm)



Fuses for Semiconductor Protection

Cylindrical Fuses

Size

6.35 x 32 mm

Rated Voltage

AC/DC 1000 V**DMI Fuse for Digital Measuring Instruments**

Class

aR

Rated Current [A]	Part No.	UL Rec.	Weight [kg/100]	Pack	
315 mA	70 172 40.0.315		0.24	100	
500 mA	70 172 40.0.500		0.24	100	
1.6 A	70 172 40.1.6		0.24	100	
2 A	70 172 40.2		0.24	100	

A 1.26" (32 mm)
B 0.25" (6.35 mm)

