

10	9	8	7	6	5	4	3	2	19038
MATERIAL NO. NYLON	ENGINEERING NO. NYLON	INSULATION NYLON COLOR	MATERIAL NO. PVC	ENGINEERING NO. PVC	INSULATION PVC COLOR	WIRE RANGE AWG / MM²	MWID	FITS MALE PLUG DIA.	
190380037	BRA-2156N	LIGHT RED	190380001	BRA-2156	RED	22-18 / 0.25-1.3	.128/(3.25)	.156/(3.96)	
190380006	BRA-2180N	LIGHT RED	190380004	BRA-2180	RED	22-18 / 0.25-1.3	.128/(3.25)	.180/(4.57)	
190380009	BRB-2156N	LIGHT BLUE	190380007	BRB-2156	DARK BLUE	16-14 / 1.0-2.6	.150/(3.81)	.156/(3.96)	
190380013	BRB-2180N	LIGHT BLUE	190380011	BRB-2180	DARK BLUE	16-14 / 1.0-2.6	.150/(3.81)	.180/(4.57)	

F


E

D

C

B

A



SALES DRAWING

- NOTE(S):
1. RECEPTACLE MATERIAL: .016/(0.41) THK BRASS
 2. RECEPTACLE FINISH: TIN PLATING
 3. MWID = MAXIMUM WIRE INSULATION DIAMETER
 4. ALL COMPONENTS ARE ROHS COMPLIANT.



REVISE DIM. EC NO: ETC2006-0450 DRWN: CYORK 2006/05/23 CHKD: JMACNEIL 2006/05/24 APPR: RDEROSS 2006/05/24	DESCRIPTION REV	QUALITY SYMBOLS ▽ - 0 ▽ - 0	GENERAL TOLERANCES (UNLESS SPECIFIED)	SCALE 5:1		DESIGN UNITS INCH	THIRD ANGLE PROJECTION	REVISE ON CAD ONLY		
				mm		INCH		TITLE FULLY INSULATED INSULK FEMALE BULLET RECEPTACLE		
				4 PLACES ± --- ± ---		DIMENSION STYLE IN/MM				
				3 PLACES ± --- ± .005		DRAWN BY DATE				
				2 PLACES ± 0.13 ± .01		DAY 97/07/07				
				1 PLACE ± 0.25 ± ---		CHECKED BY DATE				
				ANGULAR ± 1/2°		RWD 97/07/07				
DRAFT WHERE APPLICABLE		APPROVED BY DATE		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
MUST REMAIN WITHIN DIMENSIONS		RWD 97/07/07		SEE CHART		SD-19038-001		1 OF 1		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										B

8

7

6

5

4

3

2

1

B