



Aluminum electrolytic capacitors

Single-ended capacitors

Series/Type: B43867

Date: November 2008

**Long-life grade capacitors
for professional electronic ballasts****Applications**

- Energy-saving lamps
- Power supplies

Features

- High reliability
- Compact dimensions
- Extended temperature range
- RoHS-compatible

Construction


- Radial leads
- Charge-discharge proof, polar
- Aluminum case with insulating sleeve
- Minus pole marking on the insulating sleeve
- Stand-off rubber seal
- Case with safety vent

Delivery mode

Terminal configurations and packing:

- Bulk
- Taped, Ammo pack
- Cut
- Kinked
- PAPR (protection against polarity reversal):
crimped leads, J leads, bent leads

Refer to chapter "Single-ended capacitors – Taping, packing and lead configurations" for further details and ordering example.




Specifications and characteristics in brief


Rated voltage V_R	160 ... 350 V DC
Surge voltage V_S	$1.1 \cdot V_R$
Rated capacitance C_R	3.3 ... 100 μF
Capacitance tolerance	$\pm 20\% \triangleq M$
Dissipation factor $\tan \delta$ (20 °C, 120 Hz)	$V_R \leq 250$ V DC: $\tan \delta$ (max.) = 0.20 $V_R \geq 350$ V DC: $\tan \delta$ (max.) = 0.25
Leakage current I_{leak} (20 °C, 5 min)	$I_{\text{leak}} = 0.03 \mu\text{A} \cdot \left(\frac{C_R}{\mu\text{F}} \cdot \frac{V_R}{V} \right) + 15 \mu\text{A}$
Useful life 140 °C; V_R ; $I_{AC,R}$	> 1000 h
Requirements	$\Delta C/C \leq \pm 35\%$ of initial value $\tan \delta \leq 3$ times initial specified limit $I_{\text{leak}} \leq$ initial specified limit
Voltage endurance test 140 °C; V_R	1000 h
Post test requirements	$\Delta C/C \leq \pm 30\%$ of initial value $\tan \delta \leq 2$ times initial specified limit $I_{\text{leak}} \leq$ initial specified limit
Vibration resistance test	To IEC 60068-2-6, test Fc: Displacement amplitude 1.5 mm, frequency range 10 ... 2000 Hz, acceleration max. 20 g, duration 3 × 2 h. Capacitor rigidly clamped by the aluminum case.
IEC climatic category	To IEC 60068-1: $V_R \leq 250$ V: 40/140/56 (−40 °C/+140 °C/56 days damp heat test) $V_R \geq 350$ V: 25/140/56 (−25 °C/+140 °C/56 days damp heat test)
Sectional specification	IEC 60384-4


B43867
High reliability – 140 °C

Dimensional drawing


With stand-off rubber seal

Diameters (mm): 10, 12.5, 16



Dimensions and weights

Dimensions (mm)				Approx. weight g
d +0.5	l	a ±0.5	b	
10	20 +2.0	5.0	0.60 ±0.05	2.6
12.5	20 +2.0	5.0	0.60 ±0.05	3.6
12.5	25 +2.0	5.0	0.60 ±0.05	4.5
16	20 +2.0	7.5	0.80 ±0.05	5.5
16	25 +2.0	7.5	0.80 ±0.05	7.5
16	31.5 +2.0	7.5	0.80 ±0.05	7.8


Overview of available types

V_R (V DC)	160	200	250	350
Case dimensions $d \times l$ (mm)				
C_R (μ F)				
3.3				10 \times 20
3.9				10 \times 20
4.7				10 \times 20
6.8				12.5 \times 20
10		10 \times 20	10 \times 20	12.5 \times 25
15		10 \times 20	12.5 \times 20	
22	10 \times 20	12.5 \times 20	12.5 \times 25	16 \times 25
33	12.5 \times 20	12.5 \times 25	12.5 \times 25	16 \times 31.5
47	12.5 \times 25	12.5 \times 25	16 \times 31.5	
68	16 \times 20	16 \times 25		
100	16 \times 25	16 \times 31.5		

Other voltage and capacitance ratings are available upon request.


B43867
High reliability – 140 °C
Technical data and ordering codes

C_R 120 Hz 20 °C μF	Case dimensions $d \times l$ mm	$I_{AC,R}$ 120 Hz 140 °C mA	$I_{AC,R}$ 100 kHz 140 °C mA	Ordering code (composition see below)
$V_R = 160$ V DC				
22	10 × 20	145	217	B43867A1226M***
33	12.5 × 20	200	300	B43867A1336M***
47	12.5 × 25	270	405	B43867A1476M***
68	16 × 20	345	517	B43867A1686M***
100	16 × 25	450	675	B43867A1107M***
$V_R = 200$ V DC				
10	10 × 20	90	135	B43867A2106M***
15	10 × 20	120	180	B43867A2156M***
22	12.5 × 20	170	255	B43867A2226M***
33	12.5 × 25	225	337	B43867A2336M***
47	12.5 × 25	270	405	B43867A2476M***
68	16 × 25	370	555	B43867A2686M***
100	16 × 31.5	495	742	B43867A2107M***
$V_R = 250$ V DC				
10	10 × 20	95	142	B43867F2106M***
15	12.5 × 20	120	180	B43867F2156M***
22	12.5 × 25	185	277	B43867F2226M***
33	12.5 × 25	225	337	B43867F2336M***
47	16 × 31.5	330	495	B43867F2476M***
$V_R = 350$ V DC				
3.3	10 × 20	55	82	B43867A4335M***
3.9	10 × 20	65	97	B43867A4395M***
4.7	10 × 20	75	112	B43867A4475M***
6.8	12.5 × 20	90	135	B43867A4685M***
10	12.5 × 25	122	183	B43867A4106M***
22	16 × 25	210	315	B43867A4226M***
33	16 × 31.5	280	420	B43867A4336M***

Composition of ordering code
***** = Version**

000 = for standard leads, bulk

001 = for kinked leads, bulk

002 = for cut leads, bulk


 003 = for crimped leads, blister (from $d \times l = 16 \times 20$ mm to 16×31.5 mm)

004 = for J leads, blister



 008 = for taped leads, Ammo pack, lead spacing F = 5.0 mm (from $d \times l = 10 \times 20$ mm to 12.5×25 mm)

 009 = for taped leads, Ammo pack, lead spacing F = 7.5 mm (from $d \times l = 16 \times 20$ mm to 16×31.5 mm)

012 = for bent 90° leads, blister (for Ø 16 mm)


Useful life

depending on ambient temperature T_A under ripple current operating conditions¹⁾


Frequency factor of permissible ripple current I_{AC} versus frequency f


1) Refer to chapter "General technical information, 5.3 Calculation of useful life" for an explanation on how to interpret the useful life graphs.


B43867
High reliability – 140 °C

Taping, packing and lead configurations

Taping

Single-ended capacitors are available taped in Ammo pack from diameter 5 to 18 mm as follows:

Lead spacing F = 2.5 mm (\varnothing d = 5 ... 6.3 mm)


Lead spacing F = 3.5 mm (\varnothing d = 8 mm)

Lead spacing F = 5.0 mm (from $d \times l = 10 \times 12.5$ mm to 12.5×30 mm)

Lead spacing F = 7.5 mm (\varnothing d = 16 ... 18 mm).

Lead spacing 2.5 mm (\varnothing d = 5 ... 6.3 mm)

Last 3 digits of ordering code: 007




Dimensions in mm

\varnothing d	F	H	W	W ₀	W ₁	W ₂	H ₀	P	P ₀	P ₁	I ₁	t	Δh	D ₀
5	2.5	18.5	18.0	5.5	9.0	1.5	16.0	12.7	12.7	5.1	1.0	0.7	1.0	4.0
6.3														
Toler- ance	+0.8 -0.2	± 0.75	± 0.5	min.	± 0.5	max.	± 0.5	± 1.0	± 0.2	± 0.5	max.	± 0.2	max.	± 0.2


Lead spacing 3.5 mm ($\varnothing d = 8$ mm)


Last 3 digits of ordering code: 006


Dimensions in mm


$\varnothing d$	F	H	W	W_0	W_1	W_2	P	P_0	P_1	I_1	t	Δh	D_0
8	3.5	18.5	18.0	12.5	9.0	1.5	12.7	12.7	4.6	1.0	0.7	1.0	4.0
Toler- ance	+0.8 -0.2	± 1.0	± 0.5	min.	± 0.5	max.	± 1.0	± 0.2	± 0.5	max.	± 0.2	max.	± 0.2


B43867
High reliability – 140 °C
Lead spacing 5.0 mm ($\emptyset d = 5 \dots 8 \text{ mm}$)

Last 3 digits of ordering code: 008


Lead spacing 5.0 mm (from $d \times l = 10 \times 12.5 \text{ mm}$ to $12.5 \times 30 \text{ mm}$)

Last 3 digits of ordering code: 008



Dimensions in mm

$\emptyset d$	F	H	W	W_0	W_1	W_2	H_0	P	P_0	P_1	l_1	t	Δh	D_0
5	5.0	18.5	18.0	5.5	9.0	1.5	16.0	12.7	12.7	3.85	1.0	0.7	1.0	4.0
6.3							16.0	12.7	12.7	3.85				
8		20.0												
10	5.0	19.0	18.0	12.5	9.0	1.5		12.7	12.7	3.85				
12.5		19.0						12.7	12.7	3.85				
								15.0	15.0	5.0				
Toler- ance	+0.8 -0.2	±0.75	±0.5	min.	±0.5	max.	±0.5	±1.0	±0.2	±0.5	max.	±0.2	max.	±0.2



Lead spacing 7.5 mm (\varnothing d = 16 ...18 mm)

Last 3 digits of ordering code: 009



Dimensions in mm


\emptyset	F	H	W	W_0	W_1	W_2	P	P_0	P_1	I_1	t	ΔP	Δh	D_0
16 18 °	7.5	18.5	18.0	12.5	9.0	1.5	30.0	15.0	3.75	1.0	0.7	0	0	4.0
	Tolerance	± 0.8	-0.5 $+0.75$	± 0.5	min.	± 0.5	max.	± 1.0	± 0.2	± 0.5	max.	± 0.2	± 1.0	± 1.0

*) Available only for case dimensions 18×20 , 18×25 and 18×31.5 mm



B43867
High reliability – 140 °C

Packing units and box dimensions

Ammo pack



Case size d × l mm	Dimensions (mm)			Packing units pcs.
	A _{max}	B _{max}	C _{max}	
5 × 11	345	55	240	2000
6.3 × 11	345	55	290	2000
8 × 11.5	345	55	240	1000
10 × 12.5	345	55	280	750
10 × 16	345	60	200	500
10 × 20	345	60	200	500
12.5 × 20	345	65	280	500
12.5 × 25	345	65	280	500
16 × 20	315	65	275	300
16 × 25	315	65	275	300
16 × 31.5	315	65	275	300
18 × 20	315	65	275	250
18 × 25	315	65	275	250
18 × 31.5	315	65	275	250





Kinked or cut leads

Single-ended capacitors are available with kinked or cut leads. Other lead configurations also available upon request.

Kinked leads


Last 3 digits of ordering code: 001

With stand-off rubber seal




Case size $d \times l$ (mm)	Dimensions (mm) $a \pm 0.5$
10 × 20	5.0
12.5 × 20	5.0
12.5 × 25	5.0
16 × 20	7.5
16 × 25	7.5
16 × 31.5	7.5
18 × 20	7.5
18 × 25	7.5
18 × 31.5	7.5
18 × 35	7.5
18 × 40	7.5

With flat rubber seal



KAL1082-T




KAL1084-A


B43867
High reliability – 140 °C


Cut leads

Last 3 digits of ordering code: 002

With stand-off rubber seal



With flat rubber seal



Case size $d \times l$ (mm)	Dimensions (mm) $a \pm 0.5$
10 × 12.5	5.0
10 × 16	5.0
10 × 20	5.0
12.5 × 20	5.0
12.5 × 25	5.0
16 × 20	7.5
16 × 25	7.5
16 × 31.5	7.5
18 × 20	7.5
18 × 25	7.5
18 × 31.5	7.5
18 × 35	7.5
18 × 40	7.5
20 × 20	10.0
20 × 25	10.0
20 × 30	10.0
20 × 35	10.0
20 × 40	10.0
22 × 30	10.0
22 × 35	10.0
22 × 40	10.0



PAPR leads (Protection Against Polarity Reversal)


These lead configurations ensure correct placement of the capacitor on the PCB with regard to polarity. PAPR leads are available for diameters from 10 mm up to 20 mm.

There are three configurations available: Crimped leads, J leads, bent 90° leads


Crimped leads

Last 3 digits of ordering code: 003


With stand-off rubber seal




With flat rubber seal




Suggestion for PCB hole diameter



Suggestion for PCB hole diameter,
wire $\varnothing 0.8$ mm




Suggestion for PCB hole diameter,
wire $\varnothing 1.0$ mm





Case size $d \times l$ (mm)	Dimensions (mm)					
	$B \pm 0.2$	$C \pm 0.5$	$D \pm 0.1$	$E \pm 0.1$	$a \pm 0.5$	$\varnothing b$
16 × 20	1.5	3.0	1.3	0.3	7.5	0.8 ± 0.05
16 × 25	1.5	3.0	1.3	0.3	7.5	0.8 ± 0.05
16 × 31.5	1.5	3.0	1.3	0.3	7.5	0.8 ± 0.05
18 × 20	1.5	3.0	1.3	0.3	7.5	0.8 ± 0.1
18 × 25	1.5	3.0	1.3	0.3	7.5	0.8 ± 0.1
18 × 31.5	1.5	3.0	1.3	0.3	7.5	0.8 ± 0.1
18 × 35	1.5	3.0	1.3	0.3	7.5	0.8 ± 0.1
18 × 40	1.5	3.0	1.3	0.3	7.5	0.8 ± 0.1
20 × 20	1.5	3.0	1.6	0.3	10.0	1.0 ± 0.1
20 × 25	1.5	3.0	1.6	0.3	10.0	1.0 ± 0.1
20 × 30	1.5	3.0	1.6	0.3	10.0	1.0 ± 0.1
20 × 35	1.5	3.0	1.6	0.3	10.0	1.0 ± 0.1
20 × 40	1.5	3.0	1.6	0.3	10.0	1.0 ± 0.1


B43867
High reliability – 140 °C
J leads

Last 3 digits of ordering code: 004



Suggestion for PCB hole diameter

Suggestion for PCB hole diameter,
wire $\varnothing 0.6$ mm

Suggestion for PCB hole diameter,
wire $\varnothing 0.8$ mm


Case size d × l (mm)	Dimensions (mm)				
	C ± 0.5	E ± 0.5	J ± 0.2	a ± 0.5	$\varnothing b$
10 × 12.5	3.2	0.7	1.2	5.0	0.6 ± 0.05
10 × 16	3.2	0.7	1.2	5.0	0.6 ± 0.05
10 × 20	3.2	0.7	1.2	5.0	0.6 ± 0.05
12.5 × 20	3.2	0.7	1.2	5.0	0.6 ± 0.05
12.5 × 25	3.2	0.7	1.2	5.0	0.6 ± 0.05
16 × 20	3.5	0.7	1.6	7.5	0.8 ± 0.05
16 × 25	3.5	0.7	1.6	7.5	0.8 ± 0.05
16 × 31.5	3.5	0.7	1.6	7.5	0.8 ± 0.05
18 × 20	3.5	0.7	1.6	7.5	0.8 ± 0.1
18 × 25	3.5	0.7	1.6	7.5	0.8 ± 0.1
18 × 31.5	3.5	0.7	1.6	7.5	0.8 ± 0.1
18 × 35	3.5	0.7	1.6	7.5	0.8 ± 0.1


Bent 90° leads for horizontal mounting pinning

Last 3 digits of ordering code: 012



Case size $d \times l$ (mm)	Dimensions (mm)				
	$C \pm 0.5$	$E \pm 0.5$	$F \pm 0.5$	$a \pm 0.5$	$\emptyset b$
16 × 20	4.0	4.0	12.0	7.5	0.8 ± 0.05
16 × 25	4.0	4.0	12.0	7.5	0.8 ± 0.05
16 × 31.5	4.0	4.0	12.0	7.5	0.8 ± 0.05
18 × 20	4.0	4.0	13.0	7.5	0.8 ± 0.1
18 × 25	4.0	4.0	13.0	7.5	0.8 ± 0.1
18 × 31.5	4.0	4.0	13.0	7.5	0.8 ± 0.1
18 × 35	4.0	4.0	13.0	7.5	0.8 ± 0.1
18 × 40	4.0	4.0	13.0	7.5	0.8 ± 0.1

Bent leads for diameter 12.5 mm available upon request.


B43867
High reliability – 140 °C
Overview of packing units and code numbers for case sizes 5 × 11 ... 16 × 31.5

					PAPR				
Case size d × l mm	Stand- ard, bulk pcs.	Taped, Ammo pack pcs.	Kinked leads, bulk pcs.	Cut leads, bulk pcs.	Crimped leads, blister pcs.	J leads, blister pcs.	Bent 90° leads, blister pcs.		
5 × 11	2000	2000	—	—	—	—			
6.3 × 11	2500	2000	—	—	—	—			
8 × 11.5	1000	1000	—	—	—	—			
10 × 12.5	1000	750	—	1000	—	675			
10 × 16	1000	500	—	1000	—	675			
10 × 20	500	500	500	500	—	500			
12.5 × 20	350	500	350	350	—	300	¹⁾		
12.5 × 25	250	500	500	500	—	225	¹⁾		
12.5 × 30	200	—	—	—	—	—			
12.5 × 35	175	—	—	—	—	—			
12.5 × 40	175	—	—	—	—	—			
16 × 20	250	300	200	200	200	200	120		
16 × 25	250	300	200	200	200	200	120		
16 × 31.5	200	300	250	250	344	344	120		
The last three digits of the complete ordering code state the lead configuration	000	Code	F (mm)	d (mm)	001	002	003	004	012
		006	3.5	8					
		007	2.5	5...6.3					
		008	5	5...12.5					
		009	7.5	16...18					

1) Available upon request


Overview of packing units and code numbers for case sizes 18 × 20 ... 25 × 40

Case size d × l mm	Stan- dard, bulk pcs.	Taped, Ammo pack pcs.			Kinked leads, bulk pcs.	Cut leads, bulk pcs.	PAPR	
							Crimped leads, blister pcs.	J leads, blister pcs.
18 × 20	175	250			175	175	200	200
18 × 25	150	250			150	150	200	200
18 × 31.5	100	250			100	100	150	120
18 × 35	100	—			100	100	150	150
18 × 40	125	—			100	100	120	—
20 × 20	125	—			—	125	200	—
20 × 25	125	—			—	125	200	—
20 × 30	100	—			—	100	120	—
20 × 35	100	—			—	100	120	—
20 × 40	100	—			—	100	120	—
22 × 30	80	—			—	100	—	—
22 × 35	80	—			—	100	—	—
22 × 40	80	—			—	100	—	—
25 × 40	40	—			—	—	—	—
The last three digits of the complete ordering code state the lead configuration	000	Code	F (mm)	d (mm)	001	002	003	004
		007	2.5	4...6.3				
		008	5	6.3...12.5				
		009	7.5	16...18				

**B43867****High reliability – 140 °C**

Cautions and warnings

Personal safety

The electrolytes used by EPCOS have not only been optimized with a view to the intended application, but also with regard to health and environmental compatibility. They do not contain any solvents that are detrimental to health, e.g. dimethyl formamide (DMF) or dimethyl acetamide (DMAC).

Furthermore, part of the high-voltage electrolytes used by EPCOS are self-extinguishing. They contain flame-retarding substances which will quickly extinguish any flame that may have been ignited.

As far as possible, EPCOS does not use any dangerous chemicals or compounds to produce operating electrolytes. However, in exceptional cases, such materials must be used in order to achieve specific physical and electrical properties because no safe substitute materials are currently known. However, the amount of dangerous materials used in our products has been limited to an absolute minimum. Nevertheless, the following rules should be observed when handling Al electrolytic capacitors:

- Any escaping electrolyte should not come into contact with eyes or skin.
- If electrolyte does come into contact with the skin, wash the affected parts immediately with running water. If the eyes are affected, rinse them for 10 minutes with plenty of water. If symptoms persist, seek medical treatment.
- Avoid breathing in electrolyte vapor or mists. Workplaces and other affected areas should be well ventilated. Clothing that has been contaminated by electrolyte must be changed and rinsed in water.




Product safety

The table below summarize the safety instructions that must be observed without fail. A detailed description can be found in the relevant sections of chapter "General technical information".

Topic	Safety information	Reference Chapter "General technical information"
Polarity	Make sure that polar capacitors are connected with the right polarity.	1 "Basic construction of aluminum electrolytic capacitors"
Reverse voltage	Voltages polarity classes should be prevented by connecting a diode.	3.1.6 "Reverse voltage"
Upper category temperature	Do not exceed the upper category temperature.	7.2 "Maximum permissible operating temperature"
Maintenance	Make periodic inspections of the capacitors. Before the inspection, make sure that the power supply is turned off and carefully discharge the electricity of the capacitors. Do not apply any mechanical stress to the capacitor terminals.	10 "Maintenance"
Mounting position of screw terminal capacitors	Do not mount the capacitor with the terminals (safety vent) upside down.	11.1 "Mounting positions of capacitors with screw terminals"
Mounting of single-ended capacitors	The internal structure of single-ended capacitors might be damaged if excessive force is applied to the lead wires. Avoid any compressive, tensile or flexural stress. Do not move the capacitor after soldering to PC board. Do not pick up the PC board by the soldered capacitor. Do not insert the capacitor on the PC board with a hole space different to the lead space specified.	11.4 "Mounting considerations for single-ended capacitors"
Robustness of terminals	The following maximum tightening torques must not be exceeded when connecting screw terminals: M5: 2 Nm M6: 2.5 Nm	11.3 "Mounting torques"
Soldering	Do not exceed the specified time or temperature limits during soldering.	11.5 "Soldering"


B43867
High reliability – 140 °C

Topic	Safety information	Reference Chapter "General technical information"
Soldering, cleaning agents	Do not allow halogenated hydrocarbons to come into contact with aluminum electrolytic capacitors.	11.6 "Cleaning agents"
Passive flammability	Avoid external energy, such as fire or electricity.	8.1 "Passive flammability"
Active flammability	Avoid overload of the capacitors.	8.2 "Active flammability"
		Reference Chapter "Capacitors with screw terminals"
Breakdown strength of insulating sleeves	Do not damage the insulating sleeve, especially when ring clips are used for mounting.	"Screw terminals - accessories"


Symbols and terms

Symbol	English	German
C	Capacitance	Kapazität
C_R	Rated capacitance	Nennkapazität
C_S	Series capacitance	Serienkapazität
$C_{S,T}$	Series capacitance at temperature T	Serienkapazität bei Temperatur T
C_f	Capacitance at frequency f	Kapazität bei Frequenz f
d	Case diameter, nominal dimension	Gehäusedurchmesser, Nennmaß
d_{max}	Maximum case diameter	Maximaler Gehäusedurchmesser
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatzserienwiderstand
ESR_f	Equivalent series resistance at frequency f	Ersatzserienwiderstand bei Frequenz f
ESR_T	Equivalent series resistance at temperature T	Ersatzserienwiderstand bei Temperatur T
f	Frequency	Frequenz
I	Current	Strom
I_{AC}	Alternating current (ripple current)	Wechselstrom
$I_{AC,rms}$	Root-mean-square value of alternating current	Wechselstrom, Effektivwert
$I_{AC,f}$	Ripple current at frequency f	Wechselstrom bei Frequenz f
$I_{AC,max}$	Maximum permissible ripple current	Maximal zulässiger Wechselstrom
$I_{AC,R}$	Rated ripple current	Nennwechselstrom
$I_{AC,R}$ (B)	Rated ripple current for base cooling	Nennwechselstromstrom für Bodenkühlung
I_{leak}	Leakage current	Ableitstrom
$I_{leak,op}$	Operating leakage current	Ableitstrom bei Betrieb
l	Case length, nominal dimension	Gehäuselänge, Nennmaß
l_{max}	Maximum case length (without terminals and mounting stud)	Maximale Gehäuselänge (ohne Anschlüsse und Gewindegöhlen)
R	Resistance	Widerstand
R_{ins}	Insulation resistance	Isolationswiderstand
R_{symm}	Balancing resistance	Symmetrierwiderstand
T	Temperature	Temperatur
ΔT	Temperature difference	Temperaturdifferenz
T_A	Ambient temperature	Umgebungstemperatur
T_C	Case temperature	Gehäusetemperatur
T_B	Capacitor base temperature	Temperatur des Becherbodens
t	Time	Zeit
Δt	Period	Zeitraum
t_b	Service life (operating hours)	Brauchbarkeitsdauer (Betriebszeit)


B43867
High reliability – 140 °C

Symbol	English	German
V	Voltage	Spannung
V_F	Forming voltage	Formierspannung
V_{op}	Operating voltage	Betriebsspannung
V_R	Rated voltage, DC voltage	Nennspannung, Gleichspannung
V_s	Surge voltage	Spitzenspannung
X_C	Capacitive reactance	Kapazitiver Blindwiderstand
X_L	Inductive reactance	Induktiver Blindwiderstand
Z	Impedance	Scheinwiderstand
Z_T	Impedance at temperature T	Scheinwiderstand bei Temperatur T
$\tan \delta$	Dissipation factor	Verlustfaktor
λ	Failure rate	Ausfallrate
ϵ_0	Absolute permittivity	Elektrische Feldkonstante
ϵ_r	Relative permittivity	Dielektrizitätszahl
ω	Angular velocity; $2 \cdot \pi \cdot f$	Kreisfrequenz; $2 \cdot \pi \cdot f$

Notes

All dimensions are given in mm.

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CSSP, CTVS, DSSP, MiniBlue, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseMod, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EPCOS:

[B43867A1226M000](#) [B43867A1336M000](#) [B43867A1476M000](#) [B43867A1686M000](#) [B43867A1107M000](#)
[B43867A2106M000](#) [B43867A2156M000](#) [B43867A2226M000](#) [B43867A2336M000](#) [B43867A2476M000](#)
[B43867A2686M000](#) [B43867A2107M000](#) [B43867F2106M000](#) [B43867F2156M000](#) [B43867F2226M000](#)
[B43867F2336M000](#) [B43867F2476M000](#) [B43867A4335M000](#) [B43867A4395M000](#) [B43867A4475M000](#)
[B43867A4685M000](#) [B43867A4106M000](#) [B43867A4226M000](#) [B43867A4336M000](#)