


© 1953 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND OR PATENTS PENDING.

LOC	REVISIONS				
	ZONE	LTR	DESCRIPTION	DATE	APPROVED
G			REDRAWN & REVISED PG-5563	1-6-70	JME
		H	REV. PER ECN P-7000	10/23/70	JME
		J	REV. PER P-8347	9/6/79	JME
		K	OBSOLETE 2-1 P-9222	DDT 3-1-82	DTM
		L	OBSOLETE 2-2 G-2881	JT 3/8/88	DTM
		M	REV PER G-4680	JT 7/2/88	DTM



TONGUE MATERIAL THICKNESS = .040 ±.003
FOR .298 MAX WIRE INS DIA

TABLE I

1	WIRE TERMINAL	322003	BODY: COPPER (QQ-C-576)		
			FINISH: (SEE TABLE II)		
			INSULATION: PVC COLOR: RED		
			METALLIC SLEEVE: COPPER (QQ-C-576)		
			METALLIC BAND: STEEL 99-5-698 (ASTM A109)		
QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS .008 ANGLES 1°		CONTRACT NO. — 4 —	AMP AMP INCORPORATED HARRISBURG, PENNSYLVANIA		
DR. <i>J. Kant</i> 1-14-69					
CHK. <i>M. E. Ensminger</i> 1-6-70		NAME	WIRE TERMINAL		
MATERIAL		APPR. <i>L. Vahel</i> 1-7-70	AMPLI-BOND - RING TONGUE		
SEE TABLE I		REL. <i>M. E. Ensminger</i> 1-8-70	WIRE SIZE: 8		
		DSGN APPR.	SIZE	CODE IDENT NO.	NUMBER
		OTHER APPR.	B	00779	322003
			SCALE	NTS.	SHEET 1 OF 1

TABLE II

2-322003-1	GOLD PL (MIL-G-45204) TYPE II 00005 MIN EXT THK OVER NICKEL PL (QQ-N-290) 00003 MIN EXT THK.	2-322003-2	OBSOLETE
322003	TIN PL (MIL-T-10727)	2-322003-2	OBSOLETE
PART NO.	FINISH	PART No. ON TAPE	