

Features

ICE Technology*

- 115°C Maximum Case Temperature
- -40°C Minimum Temp.
- Built-in FCC/EN55022 Class B Filter
- 2:1 Wide Input Voltage Range
- 40 Watts Output Power
- Ribbed or Baseplate Case Styles
- Min. Efficiency of 87%
- 3kVDC Isolation
- Low Quiescent Current

Description

The RPP40 series 2:1 input range DC/DC converters are ideal for high end industrial applications and COTS Military applications where a very wide operating temperature range of -45°C to +120°C is required. Although the case size is very compact, the converter contains a built-in filter EN55022 Class B / FCC Level B without the need for any external components. The RPP40 is available in two case styles: the ribbed case and the baseplate case for high vibration, bulkhead-mounting or for passive cooling applications. They are UL-60950-1 certified.

Selection Guide 24V and 48V Input Types

Part Number	Input Range VDC	Output Voltage VDC	Output Current A	Efficiency ⁽²⁾ (Typ.)
RPP40-243.3S	18-36	3.3	12	87%
RPP40-2405S	18-36	5	8	89%
RPP40-2412S	18-36	12	3.33	87%
RPP40-2415S	18-36	15	2.67	88%
RPP40-2424S	18-36	24	1.67	88%
RPP40-483.3S	36-75	3.3	12	88%
RPP40-4805S	36-75	5	8	89%
RPP40-4812S	36-75	12	3.33	87%
RPP40-4815S	36-75	15	2.67	88%
RPP40-4824S	36-75	24	1.67	88%
RPP40-2412D	18-36	±12	±1.67	87%
RPP40-2415D	18-36	±15	±1.33	88%
RPP40-2424D	18-36	±24	±0.84	88%
RPP40-4812D	36-75	±12	±1.67	87%
RPP40-4815D	36-75	±15	±1.33	88%
RPP40-4824D	36-75	±24	±0.84	88%

** add suffix for case options

SUFFIX INFORMATION

none = Standard Ribbed Case
-B = Baseplate Case

For other CTRL logic (-1), case style (-F) or low temperature options (-L, -M, -T) please contact RECOM for availability.

POWERLINE+

DC/DC-Converter
with 3 year Warranty



40 Watt 2:1 Single & Dual Output



**UL-60950-1 Certified
E224736**

RPP40

* ICE Technology

ICE (Innovation in Converter Excellence) uses state-of-the-art techniques to minimise internal power dissipation and to increase the internal temperature limits to extend the ambient operating temperature range to the maximum. Refer to Application Notes

Specifications (typical at nominal input and 25°C unless otherwise noted)

Input Voltage Range	24V nominal input 48V nominal input	9-36VDC 18-75VDC	
Under Voltage Lockout	24V input 48V input	DC-DC ON (min.) DC-DC OFF (max.) DC-DC ON (min.) DC-DC OFF (max.)	17.5VDC 17VDC 35VDC 34VDC
Input Filter		Common Mode EMC Filter	
Input Voltage Variation dv/dt (Complies with ETS300 132 part 4.4)		5V/ms max	
Input Surge Voltage (100 ms max.)	24V Input 48V Input	50VDC 100VDC	
Input Reflected Ripple		nominal Vin and full load 30mA p-p	
Start Up Time		nominal Vin and constant resistor load 2ms typ., 5ms max.	
Remote ON/OFF ⁽⁴⁾	Logic High Logic Low Nominal input	Open or 3.0V < Vr < 5.5V Short or 0V < Vr < 1.2V 2mA typ.	
Remote OFF input current			
Output Power		50W max.	
Output Voltage Accuracy	10% Load and nominal Vin	±1%	
Voltage Adjustability		±10%	
Minimum Load		0%	
Line Regulation	low line, high line at full load	±0.3%	
Load Regulation	10% to 100% full load	±0.5%	
Ripple and Noise (20MHz bandwidth limited) (measured with 1µF capacitor across output)	3.3V, 5V All others	60mVp-p typ. 40mVp-p typ.	
Temperature Coefficient		±0.04%/°C max.	
Transient Response	25% load step change	200µs	
Over Load Protection	% of full load at nominal Vin	120% typ.	
Short Circuit Protection		Power Limit, automatic recovery	
Output Over Voltage Protection (refer to block diagram in Application Notes)		Converter shutdown if Vout > Vout nominal + 20%	
Isolation Voltage		Rated at 2250VDC/1 minute, Flash tested at 3000VDC/1 second	
Isolation Resistance		10MΩ min.	
Isolation Capacitance (refer to block diagram in Application Notes)		3000pF max.	
Operating Frequency		260kHz ± 40kHz Maximum	
Case Temperature		+120°C	
Storage Temperature Range		-55°C to +125°C	
Over Temperature Protection (refer to block diagram in Application Notes)		internal thermistor	
Operating Temperature Range	Ambient, Free Convection	-40°C to to see Calculation (Note 7)	
Thermal Impedance (Natural convection)	Ribbed Case: Vertical Ribbed Case: Horizontal	7.3°C/Watt 10°C/Watt	
Relative Humidity		5% to 95% RH	
Case Material ⁽⁷⁾		Aluminium	
Potting Material		Silicone (UL94-V0)	

continued on next page

Specifications (typical at nominal input and 25°C unless otherwise noted)

Weight	Ribbed Case	39g
	Basrplate Case	43g
Packing Quantity	Ribbed Case	4 pcs per Tube
	Baseplate Case	Single packed
Safety Standards		certified UL-60950-1, 1st Edition
Thermal Cycling		complies with MIL-STD-810F
Vibration		10-55Hz, 12G, 30 Min. along X, Y and Z
Conducted Emissions	EN55022	Class B
Radiated Emissions	EN55022	Class B
ESD	EN61000-4-2	Perf. Criteria B
Radiated Immunity	EN61000-4-3	Perf. Criteria A
Fast Transient ⁽⁶⁾	EN61000-4-4	Perf. Criteria B
Surge ⁽⁵⁾	EN61000-4-5	Perf. Criteria B
Conducted Immunity	EN61000-4-6	Perf. Criteria A
MTBF calculated according to BELLCORE TR-NWT-000332 ⁽⁶⁾		1989 x 10 ³ hours

Notes :

1. Typical values at nominal input voltage and no load/full load.
2. Minl values at nominal input voltage and full load.
3. The ON/OFF pin voltage is referenced to negative input. The pin is pulled high internally.
ON/OFF control is standard with positive logic: e.g. RPP40-2405S
Positive logic: 0= OFF, 1 = ON. The converter will be ON if the CTRL is left open.
4. Requires an external 100µF low ESR capacitor to meet EN61000-4-4 and EN61000-4-5
5. Case I: 50% Stress, Temperature at 50°C (Ground Benign).
6. To ensure a good all-round electrical contact, the baseplate is pressed firmly into place within the aluminium housing. The hydraulic press can leave tooling marks and deformations to both the housing and baseplate. The case is anodised aluminium, so there will be natural variations in the case colour and the aluminium is not scratch resistant. Any resultant marks, scratches and colour varations are cosmetic only and do not affect the operation or performance of the converters.
7. Example:

$$R_{th\text{case-ambient}} = 7.5^\circ\text{C/W (vertical)}$$

$$R_{th\text{case-ambient}} = 11.5^\circ\text{C/W (horizontal)}$$

$$R_{th\text{case-ambient}} = \frac{T_{case} - T_{ambient}}{P_{dissipation}}$$

$$P_{dissipation} = P_{in} - P_{out} = \frac{P_{out}}{\eta} - P_{out}$$

T_{case} = Case Temperature

$T_{ambient}$ = Environment Temperature

$P_{dissipation}$ = Internal losses

P_{in} = Input Power

P_{out} = Output Power

η = Efficiency under given Operating Conditions

$R_{th\text{case-ambient}}$ = Thermal Impedance

$$P_{dissipation} = P_{in} - P_{out} = \frac{P_{out}}{\eta} - P_{out}$$

Practical Example:

Take the RPP20-1205S with 50% load. What is the maximum ambient operating temperature? Use converter vertical in application.

$$Eff_{min} = 89\% @ V_{nom}$$

$$P_{out} = 20W$$

$$P_{out\text{app}} = 20 \times 0.5 = 10W$$

$$P_{dissipation} = \frac{P_{out}}{\eta} - P_{out}$$

$$\eta = \sim 88\% \text{ (from Eff vs Load Graph)}$$

$$P_{dissipation} = \frac{10}{0.88} - 10 = 1.36W$$


$$R_{th} = \frac{T_{casemax} - T_{ambient}}{P_{dissipation}} \rightarrow 7.5^\circ\text{C/W} = \frac{115^\circ\text{C} - T_{ambient}}{1.36W}$$

$$T_{ambient} = 104.8^\circ\text{C}$$

Typical Characteristics

RPP40-4805S


Efficiency VS Input Voltage




Recommended PCB Layout

Ribbed Case

Single Output




Dual Output



Recommended PCB Layout

Baseplate Case- suggested PCB layout



Input Fuse is recommended. Recommended fuse rating = double maximum input current, time delay type.




Input Capacitor, C1, is required to meet EN61000 Surge and Fast Transient, otherwise it is not required for normal operation.

Output Capacitors C2/C3 are recommended, but not required for normal operation. Typical capacitor values are 1 μ F MLCC

To ensure optimum thermal performance, use large areas of copper on the PCB to assist with heat dissipation and mount the converter vertically.

Package Style and Pinning (mm)

Ribbed Case (Standard - no Suffix)




Pin Connections

Pin #	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	+Vout	+Vout
4	-Vout	Com
5	Trim	-Vout
6	CTRL	CTRL


Pin Pitch Tolerance ± 0.35 mm

Typical Characteristics


Baseplate Case (-B Suffix)



Baseplate Case Fixing - Mounting onto Heatsink/Bulkhead



Baseplate Case Fixing - Anti Vibration Mounting onto PCB



The product information and specifications are subject to change without prior notice. All products are designed for non-safety critical commercial and industrial applications. The Buyer agrees to implement safeguards that anticipate the consequences of any failures that might cause harm, loss of life and/or damage property.