

DATA SHEET

LEADED POWER RESISTORS

KH, KV – Power sandfilled wirewound

UP TO 17.0 W



Product Specification – Jun. 18, 2003 V.0




Specification

Type		KH206-8	KH208-8	KH210-8	KH212-8	KH214-8	KH216-8	KH218-8
Power rating P_{70}	W	4	5	7	7	9	11	17
Resistance range		see Page 2						
E-series		E 24 (5%), E 12 (10%)						
Tolerance	%	$\pm 5, \pm 10$						
Temperature coefficient	$10^{-6} \cdot K^{-1}$	depends on value see table page 3						
max. cont. working voltage	V_{RMS}	$\sqrt{P_{70} \cdot R}$ for all Styles						
Insulation voltage (1min.)	V_{RMS}	2000						
Insulation resistance	$M\Omega$	$> 10^4$						
Derating	$^{\circ}C$	linear 70 ... 350 (0W)						
Climatic category		55/200/21						
Temperature range	$^{\circ}C$	- 55 ... 350						
Thermal resistance	KW^{-1}	65	50	40	40	30	25	15
Failure rate (Total, ϑ_0 max., 60% conf. lev.)	$10^{-9} \cdot h^{-1}$	appr. 100, depends on value						
Endurance (P_{70} , @70 $^{\circ}C$, 1000h, interm.)	$\left[\frac{\Delta R}{R} \right] \%$	$\pm 3,0$ average						
Damp heat, steady state (40 $^{\circ}C$, 93% r. h., 56d)	$\left[\frac{\Delta R}{R} \right] \%$	$\pm 2,0$						
Climatic sequence	$\left[\frac{\Delta R}{R} \right] \%$	$\pm 2,0$						
Resistance to soldering heat (260 $^{\circ}C$, 10s)	$\left[\frac{\Delta R}{R} \right] \%$	$\pm 0,2$ typ.						
Terminal strength	$\left[\frac{\Delta R}{R} \right] \%$	$\pm 1,0$						
Terminal tensile strength	N	50						
Solderability	s	2,5 Flowtime; solderglobule test IEC 60068-2-20-T						

Type		KH206-8	KH208-8	KH210-8	KH212-8	KH214-8	KH216-8	KH218-8
Standards		CECC 40202-001 and -005 applicable DIN 45921 T 202						
Marking		Printed in clear						

Dimensions in mm:



* 6mm, reduced solderability in this area

Type	Resistance range			L ₁
	Min.		Max.	
	10%	5%		
KH206-8	0R056	0R10	9K1	20 ±1,0
KH208-8	0R075	0R15	15K	25 ±1,0
KH210-8	0R11	0R33	33K	38 ±1,0
KH212-8	0R075	0R15	15K	25 ±1,0
KH214-8	0R11	0R33	33K	38 ±1,0
KH216-8	0R15	0R51	47K	50 ±1,5
KH218-8	0R27	0R91	82K	75 ±2,0

Specification

Type		KV206-3	KV208-3	KV210-3	KV212-3	KV214-3	KV216-3	KV218-3
Power rating P_{70}	W	4	5	7	7	9	11	17
Resistance range		see table Page 2						
E-series		E 24 (5%), E 12 (10%)						
Tolerance	%	$\pm 5, \pm 10$						
Temperature coefficient	$10^{-6} \cdot K^{-1}$	$\sqrt{P_{70} \cdot R}$ depends on value see table Page 3						
max. cont. working voltage	V_{RMS}	for all Styles						
Insulation voltage (1min.)	V_{RMS}	2000						
Insulation resistance	$M\Omega$	$> 10^4$						
Derating	$^{\circ}C$	linear 70 ... 350 (0W)						
Climatic category		55/200/21						
Temperature range	$^{\circ}C$	- 55 ... 350						
Thermal resistance	KW^{-1}	65	50	40	40	30	25	15
Failure rate (Total, ϑ_0 max., 60% conf. lev.)	$10^{-9} \cdot h^{-1}$	appr. 100, depends on value						
Endurance (P_{70} , @70 $^{\circ}C$, 1000h, interm.)	$\left[\frac{\Delta R}{R} \right] \%$	$\pm 3,0$ average						
Damp heat, steady state (40 $^{\circ}C$, 93% r. h., 56d)	$\left[\frac{\Delta R}{R} \right] \%$	$\pm 2,0$						
Climatic sequence	$\left[\frac{\Delta R}{R} \right] \%$	$\pm 2,0$						
Resistance to soldering heat (260 $^{\circ}C$, 10s)	$\left[\frac{\Delta R}{R} \right] \%$	$\pm 0,2$ typ.						
Terminal strength	$\left[\frac{\Delta R}{R} \right] \%$	$\pm 1,0$						
Terminal tensile strength	N	50						
Solderability	s	2,5 Flowtime; solderglobule test IEC 60068-2-20-T						
Standards		CECC 40202-002 and -006 applicable DIN 45921 T 202						




Series KV

Power Wirewound Ceramic Resistors
vertical

Marking



Printed in clear



* 6mm, reduced solderability in this area

Series KV

Power Wirewound Ceramic Resistors vertical

Dimensions in mm:

Type	Resistance range			L ₁
	Min.		Max.	
	10%	5%		
KV206-3	R056	R10	9K1	20 ±1,0
KV208-3	R075	R15	15K	25 ±1,0
KV210-3	R11	R33	33K	38 ±1,0
KV212-3	R075	R15	15K	25 ±1,0
KV214-3	R11	R33	33K	38 ±1,0
KV216-3	R15	R51	47K	50 ±1,5
KV218-3	R27	R91	82K	75 ±2,0

Series KV

Power Wirewound Ceramic Resistors vertical

Temperature coefficient:

Type	TC +400 ±50 ppm K ⁻¹	TC +0 ±40 ppm K ⁻¹	TC +0 ±10 ppm K ⁻¹
KV206	R056 ... R20	R22 ... 300R	330R ... 9K1
KV208	R075 ... R30	R33 ... 470R	510R ... 15K
KV210	R11 ... R68	R75 ... 910R	1K0 ... 33K
KV212	R075 ... R30	R33 ... 470R	510R ... 15K
KV214	R11 ... R68	R75 ... 910R	1K0 ... 33K
KV216	R15 ... 1R0	1R1 ... 1K3	1K5 ... 47K
KV218	R27 ... 1R6	1R8 ... 2K4	2K7 ... 82K

Packaging:

Type	Packaging	Pieces	Pack.-Code
KV206-3	bulk	200	B
KV208-3	bulk	200	B
KV210-3	bulk	200	B
KV212-3	bulk	200	B
KV214-3	bulk	200	B
KV216-3	bulk	200	B
KV218-3	bulk	100	B

Ordering example:

KV 206-3
Type

5
Tolerance

B
Pack.-Code

1K3
R-Value