

TOSHIBA PHOTOCOUPLER GaAs IRED & PHOTO-TRANSISTOR

TLP531, TLP532

PROGRAMMABLE CONTROLLERS


AC/DC-INPUT MODULE

SOLID STATE RELAY

The TOSHIBA TLP531 and TLP532 consist of a photo-transistor optically coupled to a gallium arsenide infrared emitting diode in a six lead plastic DIP.


TLP532 is no-base internal connection for high-EMI environments.

- Collector-Emitter Voltage : 55V (Min.)
- Current Transfer Ratio : 50% (Min.)
Rank GB : 100% (Min.)
- Isolation Voltage : 2500V_{rms} (Min.)
- UL Recognized : UL1577, File No. E67349




Weight : 0.4g

PIN CONFIGURATIONS (TOP VIEW)



1 : ANODE
2 : CATHODE
3 : N.C.
4 : EMITTER
5 : COLLECTOR
6 : BASE



1 : ANODE
2 : CATHODE
3 : N.C.
4 : EMITTER
5 : COLLECTOR
6 : N.C.

MAXIMUM RATINGS (Ta = 25°C)

CHARACTERISTIC		SYMBOL	RATING	UNIT
LED	Forward Current	I _F	70	mA
	Forward Current Derating (Ta ≥ 50°C)	ΔI _F / °C	0.93	mA / °C
	Peak Forward Current (100μs pulse, 100pps)	I _{FP}	1	A
	Reverse Voltage	V _R	5	V
	Junction Temperature	T _j	125	°C
DETECTOR	Collector-Emitter Voltage	V _{CEO}	55	V
	Collector-Base Voltage (TLP531)	V _{CB0}	80	V
	Emitter-Collector Voltage	V _{ECO}	7	V
	Emitter-Base Voltage (TLP531)	V _{EBO}	7	V
	Collector Current	I _C	50	mA
	Power Dissipation	P _C	150	mW
	Power Dissipation Derating (Ta ≥ 25°C)	ΔP _C / °C	−1.5	mW / °C
	Junction Temperature	T _j	125	°C
Storage Temperature Range		T _{stg}	−55~125	°C
Operating Temperature Range		T _{opr}	−55~100	°C
Lead Soldering Temperature (10s)		T _{sol}	260	°C
Total Package Power Dissipation		P _T	250	mW
Total Package Power Dissipation Derating (Ta ≥ 25°C)		ΔP _T / °C	−2.5	mW / °C
Isolation Voltage (AC, 1min., R.H. ≤ 60%)		BV _S	2500	V _{rms}

RECOMMENDS OPERATING CONDITIONS

CHARACTERISTIC	SYMBOL	MIN.	TYP.	MAX.	UNIT
Supply Voltage	V _{CC}	—	5	24	V
Forward Current	I _F	—	16	25	mA
Collector Current	I _C	—	1	10	mA
Operating Temperature	T _{opr}	−25	—	85	°C

INDIVIDUAL ELECTRICAL CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC		SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
LED	Forward Voltage	V_F	$I_F = 10\text{mA}$	1.0	1.15	1.3	V
	Reverse Current	I_R	$V_R = 5\text{V}$	—	—	10	μA
	Capacitance	C_T	$V = 0, f = 1\text{MHz}$	—	30	—	pF
DETECTOR	Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = 0.5\text{mA}$	55	—	—	V
	Emitter-Collector Breakdown Voltage	$V_{(BR)ECO}$	$I_E = 0.1\text{mA}$	7	—	—	V
	Collector-Base Breakdown Voltage (TLP531)	$V_{(BR)CBO}$	$I_C = 0.1\text{mA}$	80	—	—	V
	Emitter-Base Breakdown Voltage (TLP531)	$V_{(BR)EBO}$	$I_E = 0.1\text{mA}$	7	—	—	V
	Collector Dark Current	I_{CEO}	$V_{CE} = 24\text{V}$	—	10	100	nA
			$V_{CE} = 24\text{V}, T_a = 85^\circ\text{C}$	—	2	50	μA
	Capacitance (Collector to Emitter)	C_{CE}	$V = 0, f = 1\text{MHz}$	—	10	—	pF

COUPLED ELECTRICAL CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Current Transfer Ratio	I_C / I_F	$I_F = 5\text{mA}, V_{CE} = 5\text{V}$ Rank Y Rank YG Rank GR Rank GB Rank BL	50	200	600	%
			50	—	150	
			50	—	300	
			100	—	300	
			100	—	600	
			200	—	600	
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 2.4\text{mA}, I_F = 8\text{mA}$	—	—	0.4	V


ISOLATION CHARACTERISTICS (Ta = 25°C)







CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Capacitance (Input to Output)	CS	VS=0, f=1MHz	—	0.8	—	pF
Isolation Resistance	RS	VS=500V, R.H.≤ 60%	5×10 ¹⁰	10 ¹⁴	—	Ω
Isolation Voltage	BVS	AC, 1 minute	2500	—	—	V _{rms}







SWITCHING CHARACTERISTICS (Ta = 25°C)






CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Rise Time	t _r	VCC=10V IC=2mA RL=100Ω	—	2	—	μs
Fall Time	t _f		—	3	—	
Turn-on Time	t _{ON}		—	3	—	
Turn-off Time	t _{OFF}		—	3	—	
Turn-on Time	t _{ON}	RL=1.9kΩ (Fig.1) RBE=OPEN VCC=5V, IF=16mA	—	2	—	μs
Storage Time	t _s		—	15	—	
Turn-off Time	t _{OFF}		—	25	—	
Turn-on Time	t _{ON}	RL=1.9Ω (Fig.1) RBE=220kΩ (TLP531) VCC=5V, IF=16mA	—	2	—	μs
Storage Time	t _s		—	12	—	
Turn-off Time	t _{OFF}		—	20	—	


Fig.1 SWITCHING TIME TEST CIRCUIT











RESTRICTIONS ON PRODUCT USE

000707EAA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.