

High voltage NPN Darlington transistor for ignition coil

Features


- High voltage special Darlington structure
- Very rugged Bipolar technology
- High DC current gain

Application

- High ruggedness electronic ignition for small engines

Description

The device is a high voltage NPN transistor in monolithic special Darlington configuration, designed for applications such as electronic ignition for small engines (scooters, lawnmowers, chainsaws).



Product status links

[ST901T](#)

[STD901T](#)

Product summary

Order code	ST901T
Marking	901T
Package	TO-220
Packing	Tube
Order code	STD901T
Marking	D901T
Package	DPAK
Packing	Tape and reel

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{CES}	Collector-emitter voltage ($V_{BE} = 0$)	500	V
V_{CEO}	Collector-emitter voltage ($I_B = 0$)	350	V
V_{EBO}	Emitter-base voltage ($I_C = 0$)	5	V
I_C	Collector current	4	A
I_{CM}	Collector peak current ($t_p < 5$ ms)	8	A
I_B	Base current	0.5	A
I_{BM}	Base peak current ($t_p < 5$ ms)	2.5	A
P_{TOT}	Total power dissipation at $T_C = 25$ °C for ST901T	100	W
	Total power dissipation at $T_C = 25$ °C for STD901T	35	
T_{stg}	Operating junction temperature range	-65 to 150	°C
T_J	Storage temperature range		°C

Table 2. Thermal data

Symbol	Parameter	Value	Unit
R_{thJC}	Thermal resistance, junction-to-case for ST901T	1.25	°C/W
	Thermal resistance, junction-to-case for STD901T	3.57	

2 Electrical characteristics

$T_C = 25\text{ °C}$ unless otherwise specified.

Table 3. Electrical characteristics

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{CES}	Collector cut-off current	$V_{BE} = 0\text{ V}, V_{CE} = 500\text{ V}$			100	μA
		$V_{BE} = 0\text{ V}, V_{CE} = 500\text{ V}, T_C = 125\text{ °C}$ ⁽¹⁾			500	
I_{CEO}	Collector cut-off current	$I_B = 0\text{ A}, V_{CE} = 350\text{ V}$			100	μA
		$I_B = 0\text{ A}, V_{CE} = 350\text{ V}, T_C = 125\text{ °C}$ ⁽¹⁾			500	
I_{EBO}	Emitter cut-off current	$I_C = 0\text{ A}, V_{EB} = 5\text{ V}$			10	μA
$V_{CEO(sus)}$ ⁽²⁾	Collector-emitter sustaining voltage	$I_B = 0\text{ A}, I_C = 10\text{ mA}$	350			V
$V_{CE(sat)}$ ⁽²⁾	Collector-emitter saturation voltage	$I_C = 2\text{ A}, I_B = 20\text{ mA}$			2	V
$V_{BE(sat)}$ ⁽²⁾	Base-emitter saturation voltage	$I_C = 2\text{ A}, I_B = 20\text{ mA}$			1.8	V
h_{FE}	DC current gain	$I_C = 2\text{ A}, V_{CE} = 2\text{ V}$	1800		3800	
		$I_C = 4\text{ A}, V_{CE} = 2\text{ V}$	500			
	Functional test	$V_{CC} = 24\text{ V}, L = 4\text{ mH}, V_{clamp} = 350\text{ V}$	4			A
t_s	Storage time	$V_{CC} = 12\text{ V}, L = 4\text{ mH}, I_C = 2\text{ A},$		15		μs
t_f	Fall time	$V_{clamp} = 250\text{ V}, I_{B(on)} = 20\text{ mA}, V_{BE(off)} = -3\text{ V}$		1.5		μs

1. Specified by design, not tested in production.

2. Pulse test: pulse duration $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.

2.1 Electrical characteristics (curves)

Figure 1. Collector-emitter saturation voltage ($h_{FE} = 100$)




Figure 2. Base-emitter saturation voltage ($h_{FE} = 100$)




Figure 3. DC current gain ($V_{CE} = 2\text{ V}$)





Figure 4. DC current gain ($V_{CE} = 5\text{ V}$)




3 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

3.1 TO-220 type A package information

Figure 5. TO-220 type A package outline




0015988_typeA_Rev_23

Table 4. TO-220 type A package mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	4.40		4.60
b	0.61		0.88
b1	1.14		1.55
c	0.48		0.70
D	15.25		15.75
D1		1.27	
E	10.00		10.40
e	2.40		2.70
e1	4.95		5.15
F	1.23		1.32
H1	6.20		6.60
J1	2.40		2.72
L	13.00		14.00
L1	3.50		3.93
L20		16.40	
L30		28.90	
øP	3.75		3.85
Q	2.65		2.95
Slug flatness		0.03	0.10

3.2 DPAK (TO-252) type A package information

Figure 6. DPAK (TO-252) type A package outline




0068772_A_34

Table 5. DPAK (TO-252) type A mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	2.20		2.40
A1	0.90		1.10
A2	0.03		0.23
b	0.64		0.90
b4	5.20		5.40
c	0.45		0.60
c2	0.48		0.60
D	6.00		6.20
D1	4.95	5.10	5.25
E	6.40		6.60
E1	4.60	4.70	4.80
e	2.159	2.286	2.413
e1	4.445	4.572	4.699
H	9.35		10.10
L	1.00		1.50
(L1)	2.60	2.80	3.00
L2	0.65	0.80	0.95
L4	0.60		1.00
R		0.20	
V2	0°		8°

3.3 DPAK (TO-252) type C3 package information

Figure 7. DPAK (TO-252) type C3 package outline




0068772_type-C3_rev34

Table 6. DPAK (TO-252) type C3 mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	2.20	2.30	2.38
A1	0.00		0.10
A2	0.90	1.01	1.10
b	0.72		0.85
b2	0.72		1.10
b3	5.13	5.33	5.46
c	0.47		0.60
c2	0.47		0.60
D	6.00	6.10	6.20
D1	5.20	5.45	5.70
E	6.50	6.60	6.70
E1	5.00	5.20	5.40
e	2.186	2.286	2.386
H	9.80	10.10	10.40
L	1.40	1.50	1.70
L1	2.90 REF		
L2	0.51 BSC		
L3	0.90		1.25
L4	0.60	0.80	1.00
L5	0.15		0.75
L6	1.80 REF		
θ	0°		8°
θ1	5°	7°	9°
θ2	5°	7°	9°

Figure 8. DPAK (TO-252) recommended footprint (dimensions are in mm)



Notes:

- 1) This footprint is able to ensure insulation up to 630 Vrms (according to CEI IEC 664-1)
- 2) The device must be positioned within $\Phi 0.05$ A B

FP_0068772_34

Revision history

Table 7. Document revision history

Date	Version	Changes
14-Oct-2004	1	First release.
15-Jan-2005	2	DC current gain range has been modified.
25-Feb-2005	3	Added four drawings on page 3.
13-Oct-2005	4	Updated package mechanical data
11-Feb-2011	5	Inserted new order code STD901T
18-May-2023	6	Updated Section 3.1 TO-220 type A package information and Section 3.2 DPAK (TO-252) type A package information . Added Section 3.3 DPAK (TO-252) type C3 package information . Minor text changes.

Contents

1	Electrical ratings	2
2	Electrical characteristics	3
2.1	Electrical characteristics (curves)	4
3	Package information	5
3.1	TO-220 type A package information	5
3.2	DPAK (TO-252) type A package information	7
3.3	DPAK (TO-252) type C3 package information	9
	Revision history	12

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2023 STMicroelectronics – All rights reserved